

TE TERMINAL	FCI/Delphi TERMINAL	TE SEAL	FCI/Delphi SEAL	SEAL INSULATION DIAMETER RANGE
2113854-1	211CC3S2161	2113214-1	211M0010	2.80 mm MAX



- 7 TERMINAL PITCH NOT COMPATIBLE WITH MECHANICAL FEED.


*WARNING
ON INSTALLATION, SET WIRE DISC TO CRIMP HEIGHT REFERENCE SETTING
FOR LARGEST WIRE SIZE. CRIMP HEIGHT REFERENCE SETTINGS GREATER
THAN THE VALUE SHOWN MAY CAUSE DAMAGE TO THE CRIMP TOOLING,
REFER TO THE INSTRUCTION SHEET FOR PROPER SETUP AND ADJUSTMENTS.

	-	1	1	2119641-1	FEED CAM, AIR FEED	248
	-	1	1	2119082-3	CAM, SNAIL, INSULATION ADJUSTMENT	244
	-	1	1	2079764-1	WASHER, WAVE SPRING, CREST-TO-CREST	243
3	-	1	1	2119083-1	RETAINER, INSULATION DIAL	242
	-	1	1	7-18023-7	SCR, SKT HD CAP M3 X 4.0	241
	-	1	1	2844940-1	AIR FEED MODULE	238
	-	REF	REF	994970-2	COUNTER, MAGNETIC	164
	-	1	1	2844908-1	SCREW, LOCKING	99
	-	1	1	2844907-1	POST, LOCKING	98
	-	1	1	455888-5	SPACER, CRIMPER	82
	-	1	1	1803607-3	DOCUMENTATION PACKAGE	71
	-	1	1	2119740-1	TAG, IDENTIFICATION	67
	-	2	2	2168078-1	SCREW, DRIVE, RH, RoHS, 2 x .188	66
	-	1	1	2168083-2	SCR, SKT HD CAP, RoHS, M4 X 8.0	60
	-	1	1	5-18022-5	SCR, HEX HD CAP, M4 X 6.0	59
5	-	1	1	985575-3	SCR, FLT SKT HD CAP M3 X 10.0	57
	-	1	1	1338683-8	FEED PAWL	56
	-	4	4	2168083-3	SCR, SKT HD CAP, RoHS, M4 X 12.0	54
	-	2	2	1-2168083-0	SCR, SKT HD CAP, RoHS, M4 X 10	53
	-	1	1	5018030-1	NUT, HEX, REG, RoHS, M3	52
	-	1	1	811242-5	BUMPER, HOLD DOWN	51
	-	1	1	690753-2	SPACER, TONKER	50
	-	1	1	18023-9	SCR, SKT HD CAP M4 X 6.0	49
	-	1	1	1803583-9	APPLICATOR BASIC ASSEMBLY, SF	46
	-	1	1	1803515-1	RAM ASSEMBLY, SF ATLANTIC	44
	-	1	1	1803602-1	SCR, BHSC, RoHS (M8 X 25)	41
	-	1	1	1-1752356-8	SUPPORT, TERMINAL	34
	-	2	2	2079383-5	SCR, BHSC, RoHS (M4 X 20)	33
	-	2	2	2-2844962-8	SPACER, CYLINDRICAL, STRIP GUIDE	30
	-	1	1	2844992-2	ASSEMBLY, STRIP GUIDE	29
	-	1	1	455888-3	SPACER, CRIMPER	28
	-	1	1	1320928-2	STRIP GUIDE	24
	-	1	1	2168083-2	SCR, SKT HD CAP, RoHS, M4 X 8.0	21
	-	2	2	1-18028-2	WASHER, FLAT, REG M4	20
	-	1	1	2119533-1	STRIPPER, SIDE FEED	19
1	-	1	1	2119806-1	INSERT, SHEAR	13
	-	1	1	3-22280-3	SPRING, COMPRESSION	12
	-	1	1	1-356885-4	STOP, SHEAR	11
	-	1	1	2119805-1	SHEAR HOLDER, FRONT	10
	-	1	1	318707-1	FLOATING SHEAR, FRONT	9
	1	2	1	6-1803056-6	ANVIL, COMBINATION	8
	-	-	-	-	-	7
	-	-	-	-	-	6
	-	1	1	2-2119781-4	DEPRESSOR, SHEAR	5
	-	1	1	238011-4	BLOCK, CRIMPER SPACER	4
1	1	2	1	1-1803248-6	CRIMPER, INSULATION 0 PREMIUM	3
	-	1	1	455888-7	SPACER, CRIMPER	2
1	1	2	1	1-1803188-1	CRIMPER, WIRE	1
	-77	-72	2	PART NO	DESCRIPTION	ITEM NO


SHEETS 3 & 4 ARE NOT REQUIRED FOR ATLANTIC VERSION

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
A	66	-	-	SEE SHEET 1	-	-	-

FEED TYPE
PNEUMATIC






FEED SPRING SETTING POSITION
(SHOWN FROM REAR SIDE)




DETAIL A


CAM POSITION




SHEAR DEPRESSOR DETAIL



TERMINAL SUPPORT LOCATION




RAM SET-UP



FEED TRACK POSITION
GUIDE BY INSULATION BARREL

ATLANTIC VERSION
Shown on sheets 1 of 4 & 2 of 4
(Pacific version shown on sheets 3 of 4 & 4 of 4)


THIS DRAWING IS A CONTROLLED DOCUMENT FOR ATEC ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE WITHOUT NOTICE. ANY CHANGES TO THIS DRAWING SHOULD BE CONTACTED FOR THE LATEST REVISION.				DWN J. HOU 17SEP2015	 TE Connectivity Harrisburg, PA 17105-3608								
				CHK L. ZHANG 17SEP2015									
				APVD J. GUO 17SEP2015									
				PRODUCT SPEC -									
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	Ocean Side Feed Applicator -								
mm													
		0 PLC ±.0005 1 PLC ±.0005 2 PLC ±.0005 3 PLC ±.0005 4 PLC ±.0005 ANGLES ±.0005											
		FINISH -											
MATERIAL	-	WEIGHT	-	A	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO					
				00779	©=2266989			-					
Customer Accessible Production Drawing						SCALE	1:2	SHEET	2	OF	4	REV	B

SHEETS 3 & 4 ARE NOT REQUIRED FOR ATLANTIC VERSION


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
A	66	-	-	SEE SHEET 1	-	-	-

FEED TYPE

PNEUMATIC




FEED SPRING SETTING POSITION
(SHOWN FROM REAR SIDE)





DETAIL A


CAM POSITION




AIR FEED



SHEAR DEPRESSOR DETAIL




TERMINAL SUPPORT LOCATION




RAM SET-UP

ITEM 30 LOCATED AT
FRONT HOLES



FEED TRACK POSITION
GUIDE BY INSULATION BARREL

PACIFIC VERSION
Shown on sheets 3 of 4 & 4 of 4
(Atlantic version shown on sheets 1 of 4 & 2 of 4)

THIS DRAWING IS UNPUBLISHED. IT IS SUBJECT TO CHANGE WITHOUT NOTICE. ANY CHANGES TO THIS DRAWING SHOULD BE CONTACTED FOR THE LATEST REVISION.				DWN	J. HOU	17SEP2015	 TE Connectivity Harrisburg, PA 17105-3608												
				CHK	L. ZHANG	17SEP2015													
				APVD	J. GUO	17SEP2015													
DIMENSIONS:				TOLERANCES UNLESS OTHERWISE SPECIFIED:			NAME	Ocean Side Feed Applicator											
mm				PRODUCT SPEC			<table><tr><td>SIZE</td><td>CAGE CODE</td><td>DRAWING NO</td><td>RESTRICTED TO</td></tr><tr><td>A1</td><td>00779</td><td>C=2266989</td><td>-</td></tr></table>					SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	A1	00779	C=2266989	-
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO																
A1	00779	C=2266989	-																
				APPLICATION SPEC															
0 PLC ±.1																			
1 PLC ±.1																			
2 PLC ±.1																			
3 PLC ±.1																			
4 PLC ±.1																			
ANGLES				±.1															
FINISH																			
MATERIAL				WEIGHT															
-				-															
Customer Accessible Production Drawing								SCALE 1:2 SHEET 4 OF 4 REV B											