

HEATING, VENTILATION & AIR CONDITIONING SYSTEMS

INNOVATIVE SOLUTIONS

Stay ahead of the trends for increased
building comfort and control

DESIGN NAVIGATOR

SUBSYSTEMS

	1	2	3	4	5	6	Max Current Rating (A) ¹	Max Voltage Rating (V) ¹	Operating Temperature Range (°C)	SMT Compatible	Wire Range (AWG)	Wire-to-Board	Wire-to-Wire	Board-to-Board	Standards
AMP CT & Mini CT Connectors	●	●	●		●		4	125 AC	-40 to +105	●	30-22	●	●		UL, CSA
AMPMODU Interconnect System	●	●					3	250 AC	-65 to +125	●	32-20	●	●	●	UL, CSA
Antenna and Molded Interconnect Device (MID)²				●						●					
Barrier Strips and Tab Accessories	●	●			●		30	600 AC/DC	-40 to +120		30-10	●			
Circuit Breaker W-28	●				●		50	250AC/32DC	-20 to +60						UL, CSA, VDE
Circuit Protection Devices					●	●	Refer below for product details								UL, CSA, TUV
CLOUDSPLITTER Connector System			●		●		1.5 signal 5.0 power	150 AC/20 DC	-40 to +85	●	26-24		●		UL, cUL
Definite Purpose Contactors					●	●	500	900 DC	-40 to +65						UL
DIP switches	●	●	●	●			0.1	50 DC	-30 to +85	●					
Dynamic Series Connectors	●				●		65	630 AC	-55 to +105	●	30-6	●	●	●	UL, RU, CSA, TUV
Economy Power (EP) Connectors	●	●			●		11	600 AC	-25 to +105	●	22-16	●	●		UL, IEC
Eurostyle and Labeled Eurostyle Terminal Blocks	●	●	●				10	300 AC/DC	-30 to +105	●	30-12	●			UL, cUL
FASTON & Positive Lock Terminals & Splices	●	●	●		●	●	48	600 AC/DC	-40 to +250		26-10	●			UL, CSA, IEC
Flexible Printed Circuit (FPC) Connectors			●				1	200 AC	-40 to +85	●		●			VESA
Grace Inertia Connectors	●	●			●		3.5	600 AC/DC	-30 to +105		28-20	●	●		UL, CSA, IEC-GWIT
Heat Shrink Tubing					●				-30 to +250						UL, CSA
High Performance Interconnects (HPI)		●	●				3	250 AC/DC	-25 to +105	●	32-22	●			
Identification - Electrical and Warning	●	●	●	●	●	●			-30 to +120						
Identification - Rating, Rack, Panel and Cabinet	●	●	●	●	●	●			-40 to +150						UL
LCD Coaxial Embedded Display Interface (LCEDI) Connectors			●				1	100 AC	-20 to +85	●	<30	●			UL, VESA
Mass Termination Assembly (MTA), SL & CST Connectors	●	●			●		5	600 AC	-55 to +105	●	26-18	●	●		UL, CSA
Mid-Range Relays RZ, RT, ORWH, PCH, T77, RY, T75, MSR, EJ	●	●	●			●	8	20/100 AC/DC	-40 to +85						UL, CSA, VDE, SEMKO, IEC
Mini Sealed Universal MATE-N-LOK Connectors					●		9.5	600 AC	-55 to +105	●	30-16	●	●		UL, CSA, VDE
Miniature AMP-IN Connectors	●						4	250 AC			24-20	●			UL
Power Double Lock Connectors		●			●		14	300 AC	-30 to +105		20-16, 26-22	●	●		UL, CSA, IEC, VDE
Power Inductors (Noise Filtering)					●		varies*	varies*	varies*	●					
Power Relays, T9A, T92, T9E, PU 9400 and 9100	●	●			●	●	75	400 AC/DC	-40 to +85						UL, CSA, VDE, SEMKO, IEC
Releasable Poke-In Wire Connector			●				6	400 AC/DC	-30 to +105	●	22-18	●			UL, IEC
Resistors	●	●	●				varies*	varies*	varies*	●					
RJ45 Connectors	●						1.5	150 AC	-40 to +85	●	26-22	●			UL, IEC
Signal Double Lock Connectors	●	●			●		3	50 AC/DC	-30 to +105		26-20		●		UL, CSA, VDE
Signal Relays IM, P2	●	●	●			●	2	250 AC/220 DC	-40 to +85	●					UL, VDE, TUV, CQC, Industry
Slide Switches	●	●					3	20 DC	-20 to +80						
SMT Poke-in Connectors			●				5	250 AC/DC	-40 to +105	●	22-18	●			UL
Tactile Switches	●	●	●				0.05	24 DC	-35 to +105	●					
Transformers	●	●			●	●		600 AC							UL
Universal MATE-N-LOK Bulkhead Solutions					●		19	600 AC/ DC	-55 to +105		30-10		●		rUL, CSA
Universal MATE-N-LOK Connectors	●	●			●		19	600 AC	-55 to +105	●	30-10	●	●	●	UL, IEC
Vertical Screwless Inline Connector			●				2	600 AC/DC	-30 to +105		18-16	●			UL

Circuit Protection Devices (CPD)

Overcurrent Protection							Overvoltage Protection			Overtemperature Protection	Hybrid Protection	
	PolySwitch Devices	Chip Fuses				2410 Very Fast Acting Fuses	GDT	PESD	SESD	RTP Devices	2Pro Devices	PolyZen Devices
		Pulse Tolerant	0603 Very Fast Acting	Fast Acting	Slow Blow							
Compressor	●											
Motor	●											
Transformer	●									●	●	
Power Supply	●	●	●	●		●	●			●	●	●
Display	●	●	●	●	●	●		●				

- CQC - China Quality Certification
- CSA - Canadian Standard Association
- cUL - Tested to Canadian Standards by Underwriters' Laboratories
- IEC - International Electrotechnical Commission
- Industry - Meets product specific industry standards (see product page on te.com for more detail)
- RU - Recognized Under
- rUL - UL Registered
- SEMKO - Svenska Elektriska Materielkontrollanstalten
- TUV - Technischer Überwachungs-Verein
- UL - Underwriters' Laboratories
- VDE - Verband Deutscher Elektroingenieure
- VESA - Video Electronics Standards Association


¹ May vary based on application and product selection

² TE is a leading developer and manufacturer of high performance embedded and external antennas.

Visit www.antenna-te.com to learn more.

* Current rating, voltage rating, and operating temperature range may vary based on application and product selection

TE OFFERS SOLUTIONS FOR ALL YOUR HVAC NEEDS.



FEATURED PRODUCTS



[Website](#)
[Quick Reference Guide](#)
[Catalog](#)

5 Mini Sealed Universal MATE-N-LOK Connectors


- Achieve design flexibility and polarization with interchangeable contacts
- Prevent accidental mis-mating with positive locking mechanism
- Protect against humidity and moisture with IP 56 & IP 57 rating



[Website](#)

1, 2, 5 Mass Termination Assembly (MTA), SL & CST Connectors

- Reduce assembly costs with mass termination of wire
- Allow for daisy chain applications with wire feed-through capability
- Increase design flexibility with right-angle and vertical mount products and through-hole and surface mount configurations



[Website](#)
[Brochure](#)

3 Releasable Poke-In Wire Connectors

- Minimize shadowing with rounded corners
- Save space with low profile design
- Allow for repeatable, flexible wire insertion




[Website](#)
[Flyer](#)


1, 2, 5, 6 Power Relays, T9A, T92, T9E, PU 9400 and 9100

- Meet a broad range of switching requirements
- Achieve design flexibility with one or two pole configurations

TE OFFERS SOLUTIONS FOR ALL YOUR HVAC NEEDS.



FEATURED PRODUCTS



[Website](#)
[Catalog](#)

1 AMPMODU Interconnect System


- Achieve high vibration performance and reliability with polarized latching receptacles
- Reduce termination time with optional insulation displacement contacts (IDC)
- Satisfy a broad range of signal needs with easy application and a competitively priced portfolio



[Website](#)
[Flyer](#)

1 5 Circuit Breakers W-28

- Provide low cost secondary protection for many different industry applications
- Save space by combining on/off switch and circuit protection in a single unit
- Simplify assembly with snap-in mounting



[Website](#)
[Quick Reference Guide](#)
[Catalog](#)

1 2 5 Economy Power (EP) Connectors

- Achieve easy mating and unmating with positive audible latch
- Support reliability with fully seated contacts and Terminal Position Assurance (TPA)
- Facilitate simple retrofit and design-in with intermateable market design




[Website](#)
[Catalog](#)

1 2 3 5 6 FASTON & Positive Lock Terminals & Splices

- Provide PC board self-retention with kinked connector design
- Save space with miniaturized discrete wire interconnect
- Offer design flexibility with IDC and crimp termination methods

FEATURED PRODUCTS



- 1 Mid-Range Relays RZ, RT, ORWH, PCH, T77, RY, T75, MSR, EJ
 - 2
 - 3
 - 6
- Design for printed circuit board mounting with splash-resistant, flux-tight, and sealed variations
 - Enable a broad range of commercial and industrial applications with 3 to 20A current carrying capability
 - Achieve inrush currents of up to 800A with normally open or normally closed contacts


[Website](#)
[Flyer](#)



- 1 Universal MATE-N-LOK Connectors
 - 2
 - 5
- Achieve easy mating and unmating with positive audible latch
 - Improve reliability in high moisture environments with splash proof options
 - Maintain ultimate safety with egg-crated, finger-proof design

[Website](#)

[Catalog](#)



- 1 Signal Relays IM, P2
 - 2
 - 3
 - 6
- Create space-saving designs with low-profile versions
 - Provide design flexibility with SMT and Thru Hole options
 - Prevent leakage with RT V/ IP67 rated seals

[Website](#)
[Flyer](#)




- 1 Slide Switches
 - 2
- Improve product durability with electrical life cycle rating of 60,000 operations
 - Achieve design flexibility with 2-, 3-, and 4-position switch configurations
 - Eliminate hand soldering with hand insertion applicator for mounting

[Website](#)
[Catalog](#)



- 1 Transformers
 - 2
 - 5
 - 6
- Meet industry requirements with UL compliant design
 - Achieve design flexibility with various pin configurations and mounting types
 - Support a wide range of applications with ratings from 1.1VA to 150VA

[Website](#)



- 1 Power Inductors (Noise Filtering)
- Enable high frequency designs and support applications requiring noise suppression
 - Improve design flexibility with shielded and unshielded device options
 - Allow for current capability up to 38 amps

[Website](#)

LET'S CONNECT

TE Connectivity (TE) is your heating ventilation and air conditioning (HVAC) systems solution provider. With an industry focused sales and product development team dedicated to helping advance your products and designs for the HVAC market, our early involvement can help provide a systems approach that ensures component compatibility and speeds your development cycles. TE's reliable, quick to install and industry-proven innovative product solutions will help you stay ahead of the trends for increased building comfort and control.

Technical Support

te.com/support-center

Australia	+86 400-820-6015	Hungary	+36 1-2892040	Portugal	+34 91-6630420
Austria	+43 1-9056-0	India	+86 400-820-6015	Russia	+74 95-790-790-2200
Belgium	+31 73-6246999	Ireland	+1 800-882-391	Slovakia	+42 02-720-11102
Brazil	+55 11-2103-6000	Italy	+39 011-4012111	Slovenia	+38 615-602-132
China	+86 400-820-6015	Japan	+044-844-8052	South Africa	+97 150-457-0806
Czech Republic	+42 02-7201-1103	Korea	+02-3415-4607	Spain	+34 932-910-330
Denmark	+46 8-5072-5000	Latvia	+37 2-6778-673	Sweden	+46 8-5072-5000
Estonia	+37 2677-8673	Lithuania	+37 037426900	Switzerland	+41 71-447-0447
Finland	+46 8-5072-5000	Luxembourg	+31 73-6246999	Taiwan	+86 400-820-6015
France	+33 1-34-20-8686	Netherlands	+31 73-6246999	Turkey	+90 212-282-6053
Germany	+49 6151-607-1999	New Zealand	+86 400-820-6015	United Kingdom	+44 0800-267666
Greece	+97 1-4-347-0226	Norway	+46 8-5072-5000	United States of America	800-522-6752
Holland	+31 73-6246999	Poland	+48 22-4576750		

te.com

© 2014 TE Connectivity Ltd. family of companies. All Rights Reserved.
1-1773848-8 CIS CM 10/2014

2Pro, AMP, AMPMODU, CLOUDSPLITTER, FASTON, MATE-N-LOK, PolySwitch, PolyZen, TE Connectivity and TE connectivity (logo) are trademarks.

Other logos, product and Company names mentioned herein may be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this brochure are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.