






THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD		
	B7	REVISED (ECR-19-019684)	16DEC14	S.H	V.P		




- EU ROHS-RELATED RESTRICTED SUBSTANCE SPEC IN HOMOGENEOUS MATERIAL REFER TO TEC-138-702 REV.G:
 LEAD < 1000PPM, CADMIUM < 100PPM, MERCURY < 1000PPM
 CHROMIUM VI < 1000PPM, PBB <1000PPM, PBDE < 1000PPM
- HALOGEN FREE SPEC:
 CHLORINE (Cl): 900 ppm MAX.
 BROMINE (Br): 900 ppm MAX.
 CHLORINE (Cl) + BROMINE (Br): 1500 ppm MAX.



OBSOLETE

		A'SSY P/N				
DIM B		1-2129345-1	1-2129345-2	1-2129345-1	2129345-2	2129345-1
DIM A		1.2	1.2	1.4	1.2	1.4

Q'TY	FINISH/COLOR	MATERIAL	PART NAME	NO.
1	0.002mm MATTE TIN PLATING ON SOLDER AREA, 0.00127mm MIN. NICKEL UNDERPLATED ALL OVER	COPPER ALLOY	GROUND SHELL	⑤
2	0.0002mm GOLD PLATING ON CONTACT AREA, 0.002mm MATTE TIN PLATING ON SOLDER AREA, 0.002mm MIN. NICKEL UNDERPLATED ALL OVER	COPPER ALLOY	POWER CONTACT	④
1	0.0002mm GOLD PLATING ON CONTACT AREA, 0.002mm MATTE TIN PLATING ON SOLDER AREA, 0.002mm MIN. NICKEL UNDERPLATED ALL OVER	COPPER ALLOY	DETECT CONTACT	③
2	0.0002mm GOLD PLATING ON CONTACT AREA, 0.002mm MATTE TIN PLATING ON SOLDER AREA, 0.002mm MIN. NICKEL UNDERPLATED ALL OVER	COPPER ALLOY	GROUND CONTACT	②
1	BLACK	HIGH TEMPERATURE THERMO-PLASTIC (UL94V-0)	HOUSING	①
1	YELLOW			







THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DWN S.HUANG 24FEB12	TE Connectivity
	0 PLC ± - 1 PLC ± - 2 PLC ± - ±0.25 3 PLC ± - ±3° 4 PLC ± - ANGLES ± -	CHK V.PENG 24FEB12	
		APVD W.KODAMA 24FEB12	
		PRODUCT SPEC	
MATERIAL SEE TABLE	FINISH	NAME DC POWER JACK CONNECTOR DIP TYPE	RESTRICTED TO
		108-99035	SIZE A3
		501-99040	CAGE CODE 00779
		CUSTOMER DRAWING	DRAWING NO C-2129345
			SCALE 4:1
			SHEET 1 OF 3
			REV B7

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1	-	-	-



⚠ [] : CONNECTOR OUTER LINE (NO COMPONENT AREA)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	TE Connectivity		
DIMENSIONS: mm		CHK	NAME		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	DC POWER JACK CONNECTOR DIP TYPE		
0 PLC	± -	PRODUCT SPEC	SIZE	CAGE CODE	DRAWING NO
1 PLC	± -	APPLICATION SPEC	A3	00779	C-2129345
2 PLC	± -	WEIGHT	RESTRICTED TO		
3 PLC	± -		CUSTOMER DRAWING		
4 PLC	± -		SCALE	SHEET	REV
ANGLES	± -		5:1	2 OF 3	B7
FINISH	± -				

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.




© COPYRIGHT - By -

LOC DW DIST


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-


4. SHIPPING BOX DIMENSION: 445mmX445mmX270mm





A-A



DETAIL F SCALE: FREE



DETAIL G SCALE 10:1



450	5	2250
PCS/REEL	REEL/SHIPPING BOX	TOTAL Q'TY

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN																					
DIMENSIONS: mm		CHK																					
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	NAME																				
<table border="1"> <tr> <td>0 PLC</td> <td>± -</td> <td>± 0.25</td> </tr> <tr> <td>1 PLC</td> <td>± -</td> <td>± 0.25</td> </tr> <tr> <td>2 PLC</td> <td>± -</td> <td>± 0.25</td> </tr> <tr> <td>3 PLC</td> <td>± -</td> <td>± 3°</td> </tr> <tr> <td>4 PLC</td> <td>± -</td> <td>± 3°</td> </tr> <tr> <td>ANGLES</td> <td>± -</td> <td>± -</td> </tr> </table>		0 PLC	± -	± 0.25	1 PLC	± -	± 0.25	2 PLC	± -	± 0.25	3 PLC	± -	± 3°	4 PLC	± -	± 3°	ANGLES	± -	± -	PRODUCT SPEC	DC POWER JACK CONNECTOR DIP TYPE		
0 PLC	± -	± 0.25																					
1 PLC	± -	± 0.25																					
2 PLC	± -	± 0.25																					
3 PLC	± -	± 3°																					
4 PLC	± -	± 3°																					
ANGLES	± -	± -																					
MATERIAL		APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO																		
FINISH		WEIGHT	A3	00779	C-2129345																		
CUSTOMER DRAWING		SCALE	NA	SHEET	3 OF 3																		
		RESTRICTED TO	REV B7																				