
## **CUSTOMER DRAWING**



|              |                    | 'XY' = W | RE GAUG | E (AWG) |     |                  |         |          |          |
|--------------|--------------------|----------|---------|---------|-----|------------------|---------|----------|----------|
| Product Name | Product Dimensions |          |         |         |     | Cable Dimensions |         |          |          |
|              | L                  | øΑ       | øΒ      | K       | AWG | øD               | øΕ      | J±0.5    | Color of |
|              | max                | min      | min     | min     |     | max              | min     | (J±0.02) | Item 4   |
| D-101-33     |                    |          |         |         | 22  |                  |         |          | black    |
| D-101-34     | 17.0               | 4.30     | 5.00    | 150     | 22  | 4.30             | 1.78    | 7.00     | white    |
| D-101-35     | (0.670)            | (0.170)  | (0.200) | (5.900) | 20  | (0.170)          | (0.070) | (0.275)  | black    |
| D-101-36     |                    |          |         |         | 20  |                  |         |          | white    |

## **MATERIALS**

- 1. INSULATION SLEEVE: Heat-shrinkable, transparent blue, radiation cross-linked polyvinylidene fluoride.
- 2. SOLDER PREFORM WITH FLUX:

SOLDER: TYPE Sn63 per ANSI-J-STD-006. FLUX: TYPE ROL1 per ANSI-J-STD-004.


THERMAL INDICATOR: red.

- 3. MELTABLE RINGS: Thermally stabilized thermoplastic. Color: gray.
- 4. GROUND LEAD: Raychem 55A0111-XY in accordance with MIL-W-22759/32 AWG 'XY' (see table) stranded tin plated copper. Color: see table.

## **APPLICATION**

- 1. These parts are designed to provide an environment protected shield termination on cables, rated for 125°C minimum, meeting the dimensional criteria listed, having tin or silver plated copper shields.
- Temperature range: -55°C to +150°C.
   Install using TE Connectivity approved convection or infrared heating tools in accordance with Raychem process standard RCPS-100-70.

For best results, prepare the cable as shown:



| Raychem THERMOFIT DEVICES   |                |   | SOLDERSLEEVE* DEVICE WITH PRE-INSTALLED LEAD  |                       |               |                   |                  |  |
|---|----------------|---|---|-----------------------|---------------|-------------------|------------------|--|
| Unless otherwise specified dimensions are in millimeters. [Inches dimensions are shown in brackets] |                |   | D-101-3X  |                       |               |                   |                  |  |
| TOLERANCES:   | ANGLI          | ANGLES: N/A TE Connectivity reserves the right to |   | 1                     |               |                   |                  |  |
| 0.00 N/A<br>0.0 N/A<br>0 N/A  | ROUG!<br>MICRO | HNESS IN<br>ON                                    | amend this drawing at any time.<br>Users should evaluate the suitability<br>of the product for their application. |                       | REV:          | DATE: 30-Mar-2020 |                  |  |
| DRAWN BY:<br>M. FORONI  | )A             | DATE:<br>15-Jun-19                                | 998   | ECO:<br>ECO-20-004511 | SCALE:<br>NTS | SIZE:<br>A        | SHEET:<br>1 of 1 |  |

© 2020 TE Connectivity Ltd. Family of Companies. All Rights Reserved.

If this document is printed it becomes uncontrolled. Check for the latest revision.

<sup>\*</sup>TE Connectivity, TE connectivity (logo), Raychem, THERMOFIT, SolderSleeve are trademarks