



REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
04	REVISED	10/26/96	10/26/96

	DIM "A"
BEFORE CRIMPING	$\frac{.695}{17.7}$ REF
AFTER CRIMPING	$\frac{.620}{15.7}$ MAX

COMPONENT	MATERIAL	FINISH
HOUSING MOUNTING NUT BUSHING LOCKWASHER	STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303	PASSIVATE PER 00-P-35
DIELECTRIC	TFE FLUOROCARBON PER ASTM-D-1457	N/A
CENTER CONTACT	BERYLLIUM COPPER PER ASTM-B-196 OR ASTM-B-197, ALLOY C17300, CONDITION H	GOLD PLATE PER MIL-G-45204
O-RING	SILICONE RUBBER PER Z2-R-765	N/A

- NOTES:
- DESIGNED FOR USE WITH .085 DIA SEMI-RIGID CABLE
 - CAPTURED CENTER CONTACT
 - PICTORIAL VIEW IS AFTER CRIMPING
 - MIN STRAIGHT CABLE LENGTH .271
 - IT IS SUGGEST TO BEND CABLE PRIOR TO CRIMPING

.XXX = in
XX.X = mm (REF)

CABLE ENTRY DIAMETER	
HOUSING	.068
CONTACT	.021

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCE ON
 FRAC DEC ANGLES
 .125 .005 .1"

These drawings and specifications are the property of M/A-COM Incorporated and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of items without written permission.

DESIGNED BY	DATE
RG	9/25/84
CHECKED BY	DATE
RG	9/25/84
APPROVED BY	DATE
RG	9/25/84

USE ASSY PROCEDURE

NO AP 20-579

M/A-COM
an AMP company

M/A-COM, Inc.
Waltham, MA 02254

TITLE OSM BULKHEAD FEEDTHRU CABLE JACK - COMPRESSION CRIMP M39012/83-3207 CAT "F"

SIZE B	CODE CONT NO 26805	2004-8207-92	REV 04
--------	--------------------	--------------	--------

SCALE 6:1

SHEET 1 OF 1

Tyco Customer PIN 1051032
 Sheet 1 of 1
 Rev 0