

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.


ELECTRICAL	MECHANICAL	ENVIRONMENTAL
NOMINAL IMPEDANCE (OHMS) 50 ± 1	Force to Engage (Lbs MAX) 15	TEMPERATURE RATING -65° TO $+165^{\circ}$ C
Frequency Range (GHz) DC to 40	Disengage (Lbs) 5.0 MIN	Vibration MIL-STD-202, Method 204, Condition D
Volt Rating (VRMS MAX) @ Sea Level 335	Center Contact Retention: N/A	Thermal Shock MIL-STD-202, Method 107, Condition B
VSWR 1.35 MAX @ 26.5 GHz	Cable Retention: Axial: 30 Lbs. Min. Rotational: 16 In. Oz.	Corrosion - MIL-STD-202, Method 101, Condition B
Insertion Loss $.012\sqrt{F}$ GHz (dB min)	Interface per MIL-STD-348A, Figure 326-1a	
Corona, 70,000 Ft (VRMS MIN) 190	DSCC Reference Part Number: 94008ZCG-1	
Dielectric Withstanding Voltage (VRMS MIN) @ Sea Level 500		
Contact Resistance (Milliohms MAX)		
Center Contact 6.0		
Outer Contact 2.0		
Cable to Housing 0.5		
RF High Potential @ Sea Level (VRMS MIN @ 5 MHz) 325		
I.R.(Megohms MIN) 5,000		

DESIGNED FOR USE WITH $\phi.085$ [2.16] SEMI-RIGID CABLE
 CABLE ENTRY DIAMETER MINIMUM

HOUSING	.089 [2.26]
CONTACT	.021 [0.53]

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
DF	X0	REV PER ECO-07-002315	19FEB07	PY	BM

COMPONENT	MATERIAL	FINISH
HOUSING CENTER CONTACT ANTI-ROCK RING	BERYLLIUM COPPER PER ASTM B 196, ALLOY C17300, CONDITION H	GOLD PLATE PER ASTM-B-488
DIELECTRIC	TFE FLUOROCARBON PER ASTM-D-1457	N/A



1056522-1
 PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C.THOMAS 19-APR-05	Tyco Electronics Corporation Harrisburg, Pa 17105-3608																						
DIMENSIONS: INCHES		CHK R.GROSS 20-APR-05																							
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD R.GROSS 20-APR-05	NAME OSMP STRAIGHT CABLE JACK DIRECT SOLDER ATTACHMENT																						
<table border="1"> <tr><td>0 PLC</td><td>±</td><td>-</td></tr> <tr><td>1 PLC</td><td>±</td><td>-</td></tr> <tr><td>2 PLC</td><td>±</td><td>-</td></tr> <tr><td>3 PLC</td><td>±</td><td>.005 [0.13]</td></tr> <tr><td>4 PLC</td><td>±</td><td>-</td></tr> <tr><td>ANGLES</td><td>±</td><td>-</td></tr> <tr><td>FINISH</td><td></td><td></td></tr> </table>		0 PLC	±	-	1 PLC	±	-	2 PLC	±	-	3 PLC	±	.005 [0.13]	4 PLC	±	-	ANGLES	±	-	FINISH			APPLICATION SPEC 408-10114	SIZE A2	CAGE CODE 00779
0 PLC	±	-																							
1 PLC	±	-																							
2 PLC	±	-																							
3 PLC	±	.005 [0.13]																							
4 PLC	±	-																							
ANGLES	±	-																							
FINISH																									
MATERIAL SEE TABLE		WEIGHT -	DRAWING NO C=1056522																						
FINISH SEE TABLE		CUSTOMER DRAWING	SCALE 20:1	SHEET 1 OF 1																					
			RESTRICTED TO -	REV E																					