




DO NOT SCALE
DIMENSIONS IN INCH

METRIC



NOTES:

1. PLATING: SILVER, THICKNESS 0.000150 MIN
2. PLATING: ELECTRO TIN, THICKNESS 0.000040 MIN
3. PLATING: SILVER, THICKNESS 0.000120 MIN
4. PLATING: SILVER, THICKNESS 0.000100 MIN
5. PLATING: PRE TIN



WIRE RANGE :
1.0-2.5 mm²
INSULATION RANGE :
.120-.160 INCH

	5	BRASS	6-160449-7
	3	BRASS	6-160449-6
	2	BRASS	6-160449-5
	1	PH.BRONZE	6-160449-3
	2	PH.BRONZE	6-160449-2
	NONE	PH.BRONZE	6-160449-1
	NONE	BRASS	6-160449-0
6-160449-6	3	BRASS	1-160449-3
6-160449-5	2	BRASS	1-160449-2
6-160449-3	1	PH.BRONZE	1-160449-1
6-160449-2	2	PH.BRONZE	1-160449-0
6-160449-1	NONE	PH.BRONZE	160449-9
6-160449-0	NONE	BRASS	160449-8
INACTIVE	4	BRASS	160449-7
6-160449-6	3	BRASS	160449-6
6-160449-5	2	BRASS	160449-5
6-160449-0	NONE	BRASS	160449-4
6-160449-3	1	PH.BRONZE	160449-3
6-160449-2	2	PH.BRONZE	160449-2
6-160449-1	NONE	PH.BRONZE	160449-1

SUPERSEDED BY FINISH MATERIAL PARTNUMBER

CUSTOMER DRAWING FOR REFERENCE ONLY WILL NOT BE UPDATED

THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION



NAME
.250 SRS FASTIN-ON RECEPTACLE.

A4	REVISED PER ECR-20-005630	MK	BH	17APR 2020
A3	views corrected as per PD	GG	DT	19DEC16
LTR.	REVISION RECORD	DR.	CHK.	DATE
DR.:	D. KESSLER	CHK.:	P. BELNON	APP.:
DATE:	19 JAN 95	DATE:	-	L.v.SOEST
DATE:	-	DATE:	-	

DWG. No.	160449	REV. LTR.	R	SHEET	A3	1 OF 1	A4
----------	--------	-----------	---	-------	----	--------	----