



LOC	DIST	REVISIONS					
A1	-	P	LTR	DESCRIPTION	DATE	DwN	APVD
		-	-	SEE SHEET 1	-	-	-

**CODING 1**

**CODING 1**  
 COLOR BLACK  
 LEVER RIGHT  
 CABLE EXIT LEFT  
 PN 1670068 / 2177656 / 2288259

NOTES		MARKINGS FOR PINOUT CONFIGURATION		PINOUT CONFIGURATION																																																
Bemerkungen		TE PN	TE Nr.	REV																																																
				1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36	37	38	39	40	41	42	43	44	45	46	47	48	
-	299	9-2288259-9		X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	
-	247	4-2288259-7		X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	
-	246	4-2288259-6		X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	
SIPAZ	245	4-2288259-5		X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	
-	244	4-2288259-4		X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	
-	243	4-2288259-3		X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	
-	242	4-2288259-2		X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	
-	241	4-2288259-1		X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	
-	240	4-2288259-0		X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	
-	239	3-2288259-9		X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	
-	233	3-2288259-3		X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	
-	232	3-2288259-2		X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	
-	231	3-2288259-1		X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	
-	229	2-2288259-9		X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	
-	228	2-2288259-8		X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	
-	227	2-2288259-7		X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	
-	225	2-2288259-5		X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	
-	224	2-2288259-4		X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	
-	223	2-2288259-3		X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X
-	222	2-2288259-2		X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X
-	199	9-2177656-9		X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X
-	110	1-2177656-0		X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	
-	099	9-1670068-9		X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	
-	094	9-1670068-4		X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	
-	037	3-1670068-7		X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	
-	036	3-1670068-6		X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	
-	035	3-1670068-5		X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X
-	034	3-1670068-4		X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X

THIS DRAWING IS A CONTROLLED DOCUMENT.		DwN	M. KRESSMANN	19 JUL 2007
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK	G. PUCKEL	19 JUL 2007
	0 PLC ±0.1 1 PLC ±0.1 2 PLC ±0.1 3 PLC ±0.1 4 PLC ±0.1 ANGLES ±1°	APVD	G. MUMPER	23 JUL 2007
MATERIAL	FINISH	NAME		
-	-	DIFFERENT PIN OUT CONFIGURATION FOR 48 POS. MIXED RECEPTACLE HOUSING		
WEIGHT	CUSTOMER DRAWING	SIZE	A1	CAGE CODE
-	-	SCALE	1:1	DRAWING NO
RESTRICTED TO	-	SHEET	2	OF
-	-	REV	057	REV
-	-	OF	8	REV





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
A1	-	-	-	SEE SHEET 1	-	-	-

CODING 2

CODING 2  
 COLOR GREY  
 LEVER LEFT  
 CABLE EXIT RIGHT  
 PN 1719683 / 2177527 / 2288258

NOTES Bemerkungen	MARKINGS FOR PINOUT- CONFIGURATION Markierung für Pinout- Konfiguration	TE PN TE Nr.	REV	PINOUT CONFIGURATION																																																	
				BLANKED CAVITIES INDICATE CLOSED LOCATIONS Leere Felder kennzeichnen geschlossene Kammern																																																	
				WITH "X" MARKED CAVITIES INDICATE OPEN LOCATIONS Markierte Felder mit "X" kennzeichnen offene Kammern																																																	
				1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36	37	38	39	40	41	42	43	44	45	46	47	48		
-	062	6-1719683-2	0		X	X						X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X			
-	061	6-1719683-1	0	X	X	X					X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	
-	059	5-1719683-9	0	X	X				X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	
-	058	5-1719683-8	0	X					X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	
-	048	4-1719683-8	0	X					X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	
-	044	4-1719683-4	0	X					X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	
-	043	4-1719683-3	0	X					X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X
-	024	2-1719683-4	0	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X
-	023	2-1719683-3	0	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X
-	022	2-1719683-2	0	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X
-	021	2-1719683-1	0	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X
-	019	1-1719683-9	0	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X
Y285-DW 10	018	1-1719683-8	0	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	
Y285-DW 10	011	1-1719683-1	0	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	
DW 10 Man Stage 4	009	0-1719683-9	0	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	
DW 10 Man W IF	008	0-1719683-8	0	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	
DW 10 Auto 0746	007	0-1719683-7	0	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	M. KRESSMANN	19.JUL.2007	 TE Connectivity					
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK	G. PUCKEL		19.JUL.2007				
		0 PLC ±0.1 1 PLC ±0.1 2 PLC ±0.1 3 PLC ±0.1 4 PLC ±0.1 ANGLES ±1°	APVD	G. MUMPER		23.JUL.2007				
MATERIAL	FINISH	WEIGHT	NAME DIFFERENT PIN OUT CONFIGURATION FOR 48 POS. MIXED RECEPTACLE HOUSING							
-	-	-	SIZE	A1	CAGE CODE	00779	DRAWING NO	1670068	RESTRICTED TO	-
CUSTOMER DRAWING			SCALE	1:1	SHEET	4	OF	8	REV	057







LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
A1	-	-	-	SEE SHEET 1	-	-	-

CODING 3

NOTES Bemerkungen	MARKINGS FOR PINOUT- CONFIGURATION Markierung für Pinout- Konfiguration	TE PN TE Nr.	REV	PINOUT CONFIGURATION																																															
				BLANKED CAVITIES INDICATE CLOSED LOCATIONS Leere Felder kennzeichnen geschlossene Kammern																								WITH "X" MARKED CAVITIES INDICATE OPEN LOCATIONS Markierte Felder mit "X" kennzeichnen offene Kammern																							
				1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36	37	38	39	40	41	42	43	44	45	46	47	48
-	027	2-1670067-7	0	X	X		X	X	X			X	X	X		X	X	X			X	X	X		X	X	X		X	X	X		X	X	X		X	X	X		X	X	X		X	X	X				
-	017	1-1670067-7	0			X	X	X	X		X		X	X	X	X	X	X			X	X	X		X	X	X		X	X	X		X	X	X		X	X	X		X	X	X		X	X	X				
-	016	1-1670067-6	0			X	X	X	X		X		X	X	X	X	X	X			X	X	X		X	X	X		X	X	X		X	X	X		X	X	X		X	X	X		X	X	X				
-	015	1-1670067-5	0			X	X	X	X	X		X	X	X	X	X	X	X			X	X	X		X	X	X		X	X	X		X	X	X		X	X	X		X	X	X		X	X	X				
-	014	1-1670067-4	0	X	X	X	X	X	X		X		X	X	X	X	X	X			X	X	X		X	X	X		X	X	X		X	X	X		X	X	X		X	X	X		X	X	X				
Y285-14-MANALUTO-0746	013	1-1670067-3	0			X	X	X	X	X		X	X	X	X	X	X	X			X	X	X		X	X	X		X	X	X		X	X	X		X	X	X		X	X	X		X	X	X				
Y285-DW10-MANALUTO-0746	012	1-1670067-2	0	X	X	X	X	X	X		X		X	X	X	X	X	X			X	X	X		X	X	X		X	X	X		X	X	X		X	X	X		X	X	X		X	X	X				
DV 10 Man Stage 3	010	1-1670067-0	0			X	X	X				X	X			X	X	X			X	X	X		X	X	X		X	X	X		X	X	X		X	X	X		X	X	X		X	X	X				
DV6 Stage 3 0720	006	0-1670067-6	0	X	X	X	X	X	X		X		X	X	X	X	X	X			X	X	X		X	X	X		X	X	X		X	X	X		X	X	X		X	X	X		X	X	X				
N14 Auto 0820	005	0-1670067-5	0			X	X	X	X	X		X	X	X	X	X	X	X			X	X	X		X	X	X		X	X	X		X	X	X		X	X	X		X	X	X		X	X	X				
N14 Man 0720 F32	004	0-1670067-4	0			X	X	X	X	X		X	X	X	X	X	X	X			X	X	X		X	X	X		X	X	X		X	X	X		X	X	X		X	X	X		X	X	X				
DV6 Stage 4 0720	003	0-1670067-3	0	X	X	X	X	X	X		X		X	X	X	X	X	X			X	X	X		X	X	X		X	X	X		X	X	X		X	X	X		X	X	X		X	X	X				
DW 10 Man Stage 4	002	0-1670067-2	0			X	X	X				X	X	X	X	X	X	X			X	X	X		X	X	X		X	X	X		X	X	X		X	X	X		X	X	X		X	X	X				
DW 10 Auto 0746	001	0-1670067-1	0	X	X	X	X	X	X		X		X	X	X	X	X	X			X	X	X		X	X	X		X	X	X		X	X	X		X	X	X		X	X	X		X	X	X				

CODING 3  
 COLOR BROWN  
 LEVER RIGHT  
 CABLE EXIT LEFT  
 PN 1670067 / 2177543 / 2288254

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	M. KRESSMANN	19.JUL.2007		
DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK	G. PUCKEL	19.JUL.2007		
mm	0 PLC ±0.1 1 PLC ±0.1 2 PLC ±0.1 3 PLC ±0.1 4 PLC ±0.1 ANGLES ±1°	APVD	G. MUMPER	23.JUL.2007		
		PRODUCT SPEC	-			
MATERIAL	FINISH	WEIGHT	NAME		DIFFERENT PIN OUT CONFIGURATION FOR 48 POS. MIXED RECEPTACLE HOUSING	
-	-	-	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
			A1	00779	1670068	-
		CUSTOMER DRAWING	SCALE	SHEET	OF	REV
			1:1	7	8	057

