1. SCOPE

1.1. Content

This specification covers the performance, tests and quality requirements for the AMP^* receptacle connectors with ACTION PIN* posts. These receptacle connectors mate with $AMP-HDI^*$.025 square pin electrical connectors, providing a 2 piece interconnection method on .100 inch centers. Connectors are available in 2, 3 and 4 row configuration.

1.2. Qualification

When tests are performed on the subject product line, the procedures specified in AMP 109 series specifications shall be used. All inspections shall be performed using the applicable inspection plan and product drawing.

2. APPLICABLE DOCUMENTS

The following documents form a part of this specification to the extent specified herein. In the event of conflict between the requirements of this specification and the product drawing, the product drawing shall take precedence. In the event of conflict between the requirements of this specification and the referenced documents, this specification shall take precedence.

2.1. AMP Documents

- A. 109-1: General Requirements for Test Specifications
- B. 109 Series: Test Specifications as indicated in Figure 1. (Comply
- with MIL-STD-202, MIL-STD-1344 and EIA RS-364)
 C. Corporate Bulletin 401-76: Cross-reference between AMP Test
 - Specifications and Military or Commercial Documents
- D. 108-26003: Contact, ECONOMATE*, ACTION PIN
- E. 114-9010 : Application Specification
- F. 501-158 : Test Report

3. REQUIREMENTS

3.1. Design and Construction

Product shall be of the design, construction and physical dimensions specified on the applicable product drawing.

* Trademark of AMP Incorporated

Product Code: 5478

AMP incorporated Harrisburg, PA 17105-3608 LCC REV 108-9069 В TITLE CONNECTOR, RECEPTACLE 10/10 Release per H CONTACT, ACTION PIN. ECN AD-5901 91 PAGE 1 OF 7 REVISION RECORD APP DATE LTR

3.2. Material

A. Contacts:

- (1) Receptacle: Phosphor bronze, gold over nickel plating
- (2) Pin: Phosphor bronze or brass, gold over nickel plating
- B. Housing: Thermoplastic, glass filled, UL 94V-0

3.3. Ratings

- A. Current: 3 amperes maximum per contact, 2.25 amperes continuous per contact at room ambient, with not more than 2 adjacent or
 - opposing circuits carrying this current.
- B. Operating temperature: -65° to 125°C for gold contacts.

3.4. Performance and Test Description

Connectors shall be designed to meet the electrical, mechanical and environmental performance requirements specified in Figure 1. All tests are performed at ambient environmental conditions per AMP Specification 109-1 unless otherwise specified.

3.5. Test Requirements and Procedures Summary

Test Description	Requirement	Procedure
Examination of Product	Meet requirements of product drawing and AMP Spec 114-9010.	Visual, dimensional and functional per applicable inspection plan.
	ELECTRICAL	
Termination Resistance, Dry Circuit	15 milliohms maximum initial; 20 milliohms maximum final.	Subject mated contacts assembled in housing to 50 mv open circuit at 100 ma maximum, see Figure 3; AMP Spec 109-6-1.
Dielectric Withstanding Voltage	Test voltage Altitude rms feet 900 sea level 200 70,000 2 milliamperes maximum leakage current.	Test between adjacent contacts of unmated connector and between contacts and mounting hardware; AMP Spec 109-29-1.
Insulation Resistance	5000 megohms minimum initial; 1000 megohms minimum final.	Test between adjacent contacts of unmated connector and between contacts and mounting hardware; AMP Spec 109-28-4. 500 volt potential.

Figure 1 (cont)

					_
		PAGE	NO	REV	LOC
AMP	AMP incorporated Harrisburg, PA 17105-3608	2	108-9069	0	B

Test Description	Req	uirement		Procedure	
	ME	CHANICAL			
Vibration, Sinusoidal High Frequency	No discon than 1 mi note (a).		See t	ubject mated connot 15 G's, 10-2000 raversed in 20 mi hours in each of utually perpendic lanes; AMP Spec 09-21-3.	Hz nutes; 3
Physical Shock	No discon than 1 mi note (a).		greater S . See t p d e a	ubject mated conno 100 G's sawtoot ulses of 6 millis uration; 3 shocks ach direction applong the 3 mutual erpendicular plantotal 18 shocks; Appec 109-26-9.	h shoo econds in lied ly es
Mating Force	7 ounces per conta		verage M t a u i f f r A	leasure force neces on mate connector assembly after 3 anmonitored cycles acorporating free loating fixtures ate of .5 inch/mi MP Spec 109-42, contact	at a nute;
Unmating Force	.4 ounce per conta		verage M t a S	leasure force nece to unmate connecto assembly, at a rat 5 inch/minute; AM apec 109-42, cond. Calculate force pe	r e of P A.
Contact Retention	Contact s dislodge locking p	from its	normal p	apply axial load of counds to individue contacts, see Figur MP Spec 109-30.	al
Durability	See note	(a).	2 2	fate and unmate pi receptacle connect 250 cycles at a ma rate of 250 cycles LMP Spec 109-27.	ors fo
	Figu	re 1 (cor	nt)		
AMP Incorpora	ted	PAGE NO			REV

Test Description	Requirement	Procedure
	ENVIRONMENTAL	
Thermal Shock	See note (a)	Subject mated connectors to 5 cycles between -65° and 125°C; AMP Spec 109-22.
Humidity-Temperature Cycling	See note (a).	Subject mated connectors to 10 humidity- temperature cycles between 25° and 65°C at 95% RH; AMP Spec 109-23-3, method III, cond. B.
Mixed Flowing Cas	See note (a).	Subject mated connectors to environmental class III for 20 days; AMP Spec 109-85-3
Temperature Life	See note (a).	Subject mated connectors to temperature life at 118°C for 33 days duration; AMP Spec 109-43.

(a) Shall meet visual requirements, show no physical damage, and shall meet requirements of additional tests as specified in the Test Sequence in Figure 2.

Figure 1 (end)

•		PAGE	NO	REV	Foc
AMP	AMP incorporated Harrisburg, PA 17105-3608	4	108-9069	0	В

3.6. Connector Qualification and Requalification Tests and Sequences

	Test Group (a)					
Test or Examination	1	2	3	4	5	
	Test Sequence (b)					
Examination of Product	1,9	1,9	1,6	1,5	1,5	
Termination Resistance, Dry Circuit		3,7	2,5	2.4	2,4	
Dielectric Withstanding Voltage	2,7					
Insulation Resistance	3,6					
Vibration	•	5				
Physical Shock		6				
Mating Force		2				
Unmating Force		8				
Contact Retention	8					
Durability		4	_			
Thermal Shock	4		3			
Humidity-Temperature Cycling	5		4			
Mixed Flowing Gas					3(c)	
Temperature Life				3(c)		

- (a) See Para 4.1.A
- (b) Numbers indicate sequence in which tests are performed
- (c) Precondition samples with 10 cycles durability

Figure 2

4. QUALITY ASSURANCE PROVISIONS

4.1. Qualification Testing

A. Sample Selection

Connector housings and contacts shall be prepared in accordance with applicable Instruction Sheets. They shall be selected at random from current production. All test groups shall consist of 3 connectors of the greatest number of positions of each type offered. Unless otherwise specified, randomly select and identify a minimum of 12 contacts per row per test specimen for all groups.

B. Sample Preparation

Test group 1 test specimens shall not be mounted onto printed circuit wiring boards. Test groups 2, 3, 4 and 5 shall be mounted onto printed circuit wiring boards prior to testing.

C. Test Sequence

Qualification inspection shall be verified by testing samples as specified in Figure 2.

				_	
		PAGE	NO	REV	LCC
AMP	AMP Incorporated Harrisburg, PA 17105-3608	5	108-9069	0	В

4.2. Requalification Testing

If changes significantly affecting form, fit, or function are made to the product or to the manufacturing process, product assurance shall coordinate requalification testing, consisting of all or part of the original testing sequence as determined by development/product, quality, and reliability engineering.

4.3. Acceptance

Acceptance is based on verification that the product meets the requirements of Figure 1. Failures attributed to equipment, test setup, or operator deficiencies shall not disqualify the product. When product failure occurs, corrective action shall be taken and samples resubmitted for qualification. Testing to confirm corrective action is required before resubmittal.

4.4. Quality Conformance Inspection

The applicable AMP quality inspection plan will specify the sampling acceptable quality level to be used. Dimensional and functional requirements shall be in accordance with the applicable product drawing and this specification.

					_
		PAGE	NO	REV	LOC
AMP	AMP Incorporated Harrisburg, PA 17105-3608	6	108-9069	0	В




Figure 3
Termination Resistance Measurement Points

Apply Axial Load




Figure 4 Contact Retention Testing

AMP Incorporated Harrisburg, PA 17105-3608

PAGE NO 7

108-9069

REV LOC B 0