

REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN APVD
	B	STANDARDIZATION OF PLATING & SPLICING	21AUG2024	GVP KJK

1 FOR MINI-APPLICATOR CRIMPING

△2 UNDERCOATING 1.25µm Ni, SELECTIVE
0.8µm Au, NO GOLD FLASH


△3 UNDERCOATING 1.25µm Ni, SELECTIVE
0.8µm Au, GOLD FLASH ON REMAINDER (GOLD
FLASH IS NOT MANDATORY ON THE PILOTED CARRIER STRIP).

△4 ZONE I BRIGHT TIN PLATED

△5 PRE TIN PLATED 2.0µm

6 MATERIAL: PHOS BRONZE

7 SPLICING - MAXIMUM 1 LOOSE END PER
REEL IS ALLOWED.



TIN	△5	167025-3	167022-3
GOLD	△3	167025-2	167022-2
GOLD	△4 △2	167025-1	167022-1
PLATING		LOOSE PIECE	ORDER NO

WIRE RANGE: 28-32 AWG 0.03-0.09 mm ²	INSUL. RANGE: .020-.040 0.5-1.02 DIA
---	--

TE Connectivity. All Rights Reserved.

DIMENSIONS: mm	DWN	15JUN2018	MATERIAL	-	FINISH	-
	CHK	15JUN2018	TE Connectivity			
TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD	15JUN2018				
0 PLC ± -	OLSON JOSEPH					
1 PLC ± -	OLSON JOSEPH		NAME	AMPMODU MOD V RECEPTACLE		
2 PLC ± -	PRODUCT SPEC		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
3 PLC ± -	APPLICATION SPEC		A4	00779	C=167022	-
4 PLC ± -	WEIGHT					
ANGLES ± -	CUSTOMER DRAWING		SCALE	1:1	SHEET	1 OF 1
			REV B			