

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.


LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN	APVD	
DF	00	0	RADIALL DWG CONVERTED TO TYCO ACAD DWG	11/03	—	—
		1	REVISED	22APR10	RF	JM

1 FRONT AND REAR INSULATORS: THERMOSET EPOXY PER ASTM D5948
 CONTACT RETENTION CLIPS: COPPER ALLOY PER ASTM B194



2 DATE CODE: YEAR & WEEK (YY WW)

3. DESCRIPTIVE PART NUMBER: GPRBN13C1SA
 THIS INSERT CONTAINS:
 6 CAVITIES FOR SIZE 20 SOCKET CONTACTS
 4 CAVITIES FOR SIZE 16 SOCKET CONTACTS
 2 CAVITIES FOR SIZE 12 SOCKET CONTACTS
 1 CAVITY FOR 5 SOCKET CONTACTS

4. THIS PRODUCT IS SOLD BY TYCO ELECTRONICS
 UNDER A LICENSE FROM RADIALL SA.



MATING FACE



THIS PRINT IS
PRELIMINARY
 UNQUALIFIED PRODUCT
 CONTACT PRODUCT ENGINEERING
 BEFORE USING THIS PRINT

1738110-1
 PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R FLAIG NOV03	Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]		CHK J MOSIER NOV03	NAME GPR-B SOCKET INSERT CLASS N CONTACT ARRANGEMENT 13C1 KEY A	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.05 [.002] 3 PLC ± - 4 PLC ± - ANGLES ± -		APVD J MOSIER NOV03	PRODUCT SPEC	RESTRICTED TO
MATERIAL		FINISH	WEIGHT	SCALE
1		-	-	1:1
		CUSTOMER DRAWING	SIZE A2	SHEET 1 OF 1
			CAGE CODE 00779	REV 1
			DRAWING NO 1738110	