

SMD AEC-Q200 QUALIFIED THICK FILM CHIP RESISTOR


TYPE CRGCQ SERIES

INTRODUCTION

TE Connectivity is pleased to introduce our AEC-Q200 qualified thick film chip resistor, suitable for auto placement in volume and for most applications. Available in seven different packages and supplied on tape and reel for automatic insertion processes. Standard values – E24 Series.

FEATURES

- Small size and light weight
- Suitable for both wave and reflow soldering techniques
- Supplied on tape
- AEC-Q200 qualified
- 7 different package sizes
- Terminal finish matte Sn over Ni
- Moisture Sensitive Level 1



INDUCTANCE AND RATED CURRENT RANGES

Type	CRGCQ0402	CRGCQ0603	CRGCQ0805	CRGCQ1206	CRGCQ1210	CRGCQ2010	CRGCQ2512
Power Rating @ 70°C	0.0625W	0.1W	0.125W	0.25W	0.5W	0.75W	1W
Jumper Rated current	1A	1A	2A	2A	2A	2A	2A
Max. Jumper Current	2A	2A	5A	10A	10A	10A	10A
Max. Working Voltage	50V	75V	150V	200V	200V	200V	200V
Max. Overload Voltage	100V	150V	300V	400V	500V	500V	500V
Dielectric Withstand Voltage	100V	300V	500V	500V	500V	500V	500V
Jumper resistance	<50mΩ						
Temperature Range	-55°C ~ +155°C						
Ambient Temperature	70°C						

SMD AEC-Q200 Qualified Thick Film Chip Resistor

Type CRGCQ series

ENVIRONMENTAL CHARACTERISTICS


Characteristics	Limits	Test Methods	
Load life	±1%: ±(1.0%+0.1Ω)Max. ±5%: ±(3.0%+0.1Ω)Max.	125°C, 35% power, at RCWV or Max. Working Voltage whichever less, 1,000 hours (1.5 hours "ON", 0.5 hours "OFF"), Measurement at 24±2 hours after test conclusion. (MIL-STD-202 Method 108)	
Temperature coefficient	1Ω ≤ R ≤ 10Ω: ±400PPM/°C 10Ω < R ≤ 100Ω: ±200PPM/°C R > 100Ω: ±100PPM/°C	Measure between -55°C ~ +125°C	
Short-time overload	±1%: ±(1.0%+0.1Ω) Max. ±5%: ±(2.0%+0.1Ω) Max.	2.5x Rated voltage or Max. Overload Voltage whichever is lower for 5 seconds, then check the resistance.	
Terminal bending	±(1.0%+0.05Ω) Max.	Bending Distance 3mm, Duration: 60s±5s, then check the resistance	
Solderability	95% coverage Min.	245±3°C; 2-3s	
Soldering heat	±(1.0%+0.05Ω) Max.	260±5°C; 10±1s	
Moisture resistance	1%: ± (0.5%+0.1Ω) Max. 5%: ± (3.0%+0.1Ω) Max.	25°C-65°C, 90-100%RH, 2.5Hr; 65°C 90-100%RH, 3Hr; 65°C-25°C 80-100%RH, 2.5Hr, 10 cycles. Measurement at 24 hours after test conclusion (MIL-STD-202 Method 106)	
Biased humidity	1%: ± (1.0%+0.1Ω) Max. 5%: ± (3.0%+0.1Ω) Max.	10% rated power, 85°C/85%RH, 1000Hr. Measurement at 24 hours after test conclusion. (MIL-STD-202 Method 103)	
Dielectric withstand voltage	No evidence of flashover, mechanical damage, arcing or insulation breakdown	Resistor shall be clamped in the trough of 90° metallic V-block and shall be tested at AC potential respectively specified in the given list of each product type for 60-70s.	
Temperature cycling	1%: ± (0.5%+0.1Ω) Max. 5%: ± (1.0%+0.1Ω) Max.	-55±3°C 30min -normal temperature 10min-15min-155±2°C 30min-normal temperature 10min-15min 1000 cycles. Measurement at 24 hours after test conclusion. (JESD22 Method JA-104)	
ESD	±(1.0%+0.05Ω) Max.		
	Chip Size	ESD	Class
	0402	0.6kv	1B
	0603	1kv	1C
	0805	1.3kv	1C
	1206	2.1kv	2
	1210	3.9kv	2
	2010	10kv	5A
2512	17kv	5C	
Sulfuration test	1%: ± (1.0%+0.1Ω) Max. 5%: ± (5.0%+0.1Ω) Max.	H2S 3-5PPM 50°C±2°C 91%-93% RH 1000H	

SMD AEC-Q200 Qualified Thick Film Chip Resistor


Type CRGCQ series

POWER DERATING CURVE

Power rating based on continuous load operation in ambient temperature of -55 - 70°C. For resistors operated in ambient temperatures above 70°C, power rating must be derated in accordance with this curve.




PULSE CHARACTERISTICS



SMD AEC-Q200 Qualified Thick Film Chip Resistor


Type CRGCQ series

DIMENSIONS



Type	Dimension (mm)				
	L	W	H	A	B
CRGCQ0402	1.00±0.10	0.50±0.05	0.35±0.05	0.20±0.10	0.25±0.10
CRGCQ0603	1.60±0.10	0.80±0.10	0.45±0.10	0.30±0.20	0.30±0.20
CRGCQ0805	2.00±0.15	1.25+0.15/-0.10	0.55±0.10	0.40±0.20	0.40±0.20
CRGCQ1206	3.10±0.15	1.55+0.15/-0.10	0.55±0.10	0.45±0.20	0.45±0.20
CRGCQ1210	3.10±0.10	2.60±0.20	0.55±0.10	0.50±0.25	0.50±0.20
CRGCQ2010	5.00±0.10	2.50±0.20	0.55±0.10	0.60±0.25	0.50±0.20
CRGCQ2512	6.35±0.10	3.20±0.20	0.55±0.10	0.60±0.25	0.50±0.20

CONSTRUCTION



1. High purity alumina substrate
2. Protective coating
3. Resistive element
4. Termination (inner) Ni/Cr
5. Termination (between) Ni Barrier
6. Termination (outer) Sn

SMD AEC-Q200 Qualified Thick Film Chip Resistor

Type CRGCQ series

POWER RATING AND RESISTANCE RANGE

Type	Power Rating @ 70°C	Tolerance	Resistance Range	Standard Series
CRGCQ0402	0.0625W	Jumper	< 50mΩ	E24 E96 by negotiation
		±1%	1R0 - 10M	
		±5%	1R0 - 10M	
CRGCQ0603	0.1W	Jumper	< 50mΩ	E24 E96 by negotiation
		±1%	1R0 - 10M	
		±5%	1R0 - 10M	
CRGCQ0805	0.125W	Jumper	< 50mΩ	E24 E96 by negotiation
		±1%	1R0 - 10M	
		±5%	1R0 - 10M	
CRGCQ1206	0.25W	Jumper	< 50mΩ	E24 E96 by negotiation
		±1%	1R0 - 10M	
		±5%	1R0 - 10M	
CRGCQ1210	0.5W	Jumper	< 50mΩ	E24 E96 by negotiation
		±1%	1R0 - 10M	
		±5%	1R0 - 10M	
CRGCQ2010	0.75W	Jumper	< 50mΩ	E24 E96 by negotiation
		±1%	1R0 - 10M	
		±5%	1R0 - 10M	
CRGCQ2512	1W	Jumper	< 50mΩ	E24 E96 by negotiation
		±1%	1R0 - 10M	
		±5%	1R0 - 10M	

MARKING

E24 series 0603 - 2512 3 Digits - first two digits denote significant figures of resistance and third digit denotes number of zeros thereafter. EG

	222	
--	-----	--

 =
 2K2

Marking for E96 Series 0805 - 2512 4 digits - First three digits denote significant figures of resistance and fourth digit denotes number of zeros thereafter. EG.

	1000	
--	------	--

 =
 100R

For ohmic values below 100R letter "R" denotes decimal point. EG

	1R80	
--	------	--

 =
 1R8 / 1.8Ω

0402 size chips are not marked


0603 E96 3 digit marking.

SMD AEC-Q200 Qualified Thick Film Chip Resistor

Type CRGCQ series


PACKAGING SPECIFICATION

Paper taping



Type	A ± 0.2	B ± 0.2	C ± 0.05	ØD +0.1 -0	E ± 0.1	F ± 0.05	G ± 0.1	W ± 0.2	T ± 0.1
0402	0.65	1.15	2.0	1.5	1.75	3.5	4.0	8.0	0.45
0603	1.10	1.90	2.0	1.5	1.75	3.5	4.0	8.0	0.67
0805	1.65	2.40	2.0	1.5	1.75	3.5	4.0	8.0	0.81
1206	2.00	3.60	2.0	1.5	1.75	3.5	4.0	8.0	0.81
1210	2.80	3.50	2.0	1.5	1.75	3.5	4.0	8.0	0.75
2010	2.80	5.40	2.0	1.5	1.75	3.5	4.0	12.0	0.75


Embossed Taping



Type	A ± 0.2	B ± 0.2	C ± 0.05	ØD +0.1 -0	ØD1 +0.1 -0	E ± 0.1	F ± 0.05	G ± 0.1	W ± 0.2	T ± 0.1
2512	3.50	6.70	2.0	1.5	1.5	1.75	5.5	4.0	12.0	1.0

Peeling strength of cover tape:


Test condition: 0.1 to 0.7 N at a peel off speed of 300mm / min.



SMD AEC-Q200 Qualified Thick Film Chip Resistor

Type CRGCQ series

REEL DIMENSIONS (mm)




Type	Tape	Reel Qty	A ± 0.5	B ± 0.5	C ± 0.5	D ± 1	M ± 2	W ± 1
0402	Paper	10,000	2	13	21	60	178	10
0603	Paper	5,000	2	13	21	60	178	10
0805	Paper	5,000	2	13	21	60	178	10
1206	Paper	5,000	2	13	21	60	178	10
1210	Paper	5,000	2	13	21	60	178	10
2010	Paper	4,000	2	13	21	60	178	13.8
2512	Embossed	4,000	2	13	21	60	178	13.8

LABEL

1. TE Product Number
2. Product Description
3. Quantity
4. Lot Number
5. RoHS Statement

Example

TYCO Pn	CRGCQ0603F100R		
DESC	CRGCQ 0603 100R 1%		
QTY	5000 Pcs.	PPM:	
LOT	SAMPLE		
REF	RoHS 2011/65/EU		
			

SMD AEC-Q200 Qualified Thick Film Chip Resistor

Type CRGCQ series

ENVIRONMENT RELATED SUBSTANCE

This product complies to EU RoHS directive, EU PAHs directive, EU PFOS directive and Halogen free.

OZONE LAYER DEPLETING SUBSTANCES

Ozone depleting substances are not used in our manufacturing process of this product.

This product is not manufactured using Chloro fluorocarbons (CFCs), Hydrochlorofluorocarbons (HCFCs), Hydrobromofluorocarbons (HBFCs) or other ozone depleting substances in any phase of the manufacturing process.

STORAGE CONDITION (MSL1)

The performance of these products, including the solderability, is guaranteed for a year from the date of arrival at your company, provided that they remain packed as they were when delivered and stored at a temperature of $25^{\circ}\text{C} \pm 10^{\circ}\text{C}$ and a relative humidity of $60\%RH \pm 10\%RH$, chemical and dust free atmosphere

Even within the above guarantee periods, do not store these products in the following conditions otherwise, their electrical performance and/or solderability may be deteriorated, and the packaging materials (e.g. taping materials) may be deformed or deteriorated, resulting in mounting failures.

1. In salty air or in air with a high concentration of corrosive gas, such as Cl_2 , H_2S , NH_3 , SO_2 , or NO_2
2. In direct sunlight

SOLDER PROFILE

Wave soldering condition: (2 cycles Max.)

Pre-heat : $100 - 120^{\circ}\text{C}$, 30 ± 5 sec.

Peak temp.: 260°C

Reflow soldering condition: (2 cycles Max.)


Pre-heat : $150 - 180^{\circ}\text{C}$, $90 - 120$ sec.

Suggestion solder temp.: $235 - 255^{\circ}\text{C}$, $20 - 40$ sec.


Peak temp.: 260°C

Hand Soldering condition:

The Soldering iron tip should be less than 300°C and maximum contact time should be 5 seconds.



RECOMMENDED PCB LAYOUT PLAN



Type	a (mm)	b (mm)	c (mm)
0402	0.45 to 0.55	1.35 to 1.45	0.45 to 0.55
0603	0.85 to 0.95	2.05 to 2.15	0.75 to 0.85
0805	0.90 to 1.10	2.90 to 3.10	1.20 to 1.40
1206	1.90 to 2.10	4.10 to 4.30	1.50 to 1.70
1210	1.90 to 2.10	4.10 to 4.30	2.50 to 2.70
2010	3.50 to 3.70	6.10 to 6.30	2.50 to 2.70
2512	4.90 to 5.10	8.10 to 8.30	3.20 to 3.40

ORDERING INFORMATION

Part Number			
CRGCQ	0603	J	10K

Common Part

CRGCQ	AEC-Q200 Qualified Thick Film Chip Resistor
-------	---

Size

0402
0603
0805
1206
1210
2010
2512

Tolerance

F	±1%
J	±5%

Resistance Value

1 ohm	(1Ω) 1R0
1K ohm	(1000Ω) 1K0
100K ohm	(100000Ω) 100K
1M ohm	(1000000Ω) 1M0

te.com

©2023 TE Connectivity. All Rights Reserved.

TE Connectivity, TE connectivity (logo) and Every Connection Counts are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this document, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any changes to the information contained herein without prior notice. TE Connectivity assumes only those obligations set forth in the terms and conditions for this product and shall in no event be liable for any incidental, indirect, or consequential damages arising out of the sale, resale, use, or misapplication of the product. TE expressly disclaims any implied warranties with respect to the information contained herein, including, but not limited to, implied warranties of merchantability or fitness for a particular purpose. Dimensions, specifications and/or information contained herein are for reference purposes only and are subject to change without notice. Consult TE for the latest dimensions, specifications and/or information. Users of TE Connectivity products must make their own assessment as to whether the respective product is suitable for the respective desired application.

08/24 ED