




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	0		I	PRELIMINARY	27APR2006	SW	CR

D

D

C


C



1776660-3 AS SHOWN

B

B




1. MATERIALS AND FINISH:
HOUSING: NYLON OR POLYESTER, HIGH TEMPERATURE COMPATIBLE,
UL 94-V0, COLOR: BLACK.
TERMINAL: PHOSPHOR BRONZE, TIN PLATED.
2. SUITABLE FOR 1,6-2, 4mm PC BOARD THICKNESS.
3. RECOGNIZED UNDER THE COMPONENT PROGRAM OF
UNDERWRITERS LABORATORIES INC.FILE N° E60677.
4. IMQ CERTIFICATE WITH SURVEILLANCE IN CONFORMITY
WITH IEC 998-1/998-2-1.}

THIS PRINT IS
PRELIMINARY
PRIOR TO CUSTOMER ORDER
CONTACT PRODUCT ENGINEERING
BEFORE USING THIS PRINT

A

A



RECOMMENDED PC BOARD LAYOUT

REEL	37.38	7	1776660-7
REEL	32.30	6	1776660-6
REEL	22.14	4	1776660-4
REEL	17.06	3	1776660-3
REEL	11.98	2	1776660-2
PACKAGING TYPE	L	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.				DWN S. WELDON	27APR2006	AMP Tyco Electronics Harrisburg, PA 17105-3608			
				CHK C. RICHARD	27APR2006				
				APVD C. RICHARD	27APR2006	NAME TERMINAL BLOCK HEADER ASSEMBLY, 90 DEGREE, CLOSED ENDS, HIGH TEMPERATURE, 5.08mm PITCH			
				PRODUCT SPEC -					
				APPLICATION SPEC -		SIZE A2	CAGE CODE 00779	DRAWING NO C-1776660	RESTRICTED TO -
				WEIGHT -		CUSTOMER DRAWING			
				CUSTOMER DRAWING					
DIMENSIONS: mm				TOLERANCES UNLESS OTHERWISE SPECIFIED:		SCALE 4:1			
				0 PLC ±. 1 PLC ±0.2 2 PLC ±. 3 PLC ±. 4 PLC ±. ANGLES ±. FINISH		SHEET 1 OF 1 REV 1			
MATERIAL 									