

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT — TE Connectivity Ltd.


| REVISIONS |     |                           |           |     |      |
|-----------|-----|---------------------------|-----------|-----|------|
| P         | LTR | DESCRIPTION               | DATE      | DWN | APVD |
|           | D   | REV PER ECR 05-009599     | 06DEC05   | JR  | TM   |
|           | D1  | REVISED PER ECO-17-014338 | 16MAY2018 | RS  | DR   |

D

C

B

A



- 1 STAMP AMP 16-14\* APPROX AS SHOWN
- 2 WIRE INSULATION DIA:  
2.667-3.683[.105-.145]
- 3 BODY THICKNESS IS  
0.787±0.051[.031±.002]
- 4 APPLIES FROM EDGE OF METAL WIRE  
BARREL TO CENTER OF STUD HOLE
- 5 600 VOLT MAX
- 6 CIRCULAR MIL AREA,  
2,050 - 5,180[1.04mm<sup>2</sup>-2.62mm<sup>2</sup>]
- 7 MAXIMUM TEMP 105°C[221°F]

|             |      |            |
|-------------|------|------------|
| TAPE & REEL | 4000 | 2-130099-1 |
| PACKAGING   | QTY  | PART NO    |

|                                                                           |  |                                                             |                                                                                                            |                    |                        |
|---------------------------------------------------------------------------|--|-------------------------------------------------------------|------------------------------------------------------------------------------------------------------------|--------------------|------------------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                    |  | DWN<br>jr ruth<br>06DEC05                                   |  TE Connectivity Ltd. |                    |                        |
| DIMENSIONS:<br>mm [INCHES]                                                |  | CHK<br>T MICHELUTTI<br>06DEC05                              |                                                                                                            |                    |                        |
| TOLERANCES UNLESS<br>OTHERWISE SPECIFIED:                                 |  | APVD<br>T MICHELUTTI<br>06DEC05                             | NAME<br>TERMINAL, RING TONGUE, PLASTI-GRIP,<br>16-14 AWG                                                   |                    |                        |
| MATERIAL<br>BODY:<br>COPPER PER ASTM B152<br>INSULATION: PVC              |  | PRODUCT SPEC<br>—<br>APPLICATION SPEC<br>114-2161<br>WEIGHT |                                                                                                            |                    |                        |
| FINISH<br>BODY:<br>TIN PLATE PER ASTM B545<br>INSULATION:<br>COLOR - BLUE |  | CUSTOMER DRAWING                                            | SIZE<br>A3                                                                                                 | CAGE CODE<br>00779 | DRAWING NO<br>C-130099 |
|                                                                           |  |                                                             | RESTRICTED TO<br>—                                                                                         | SCALE<br>5:1       | SHEET<br>1 of 1        |
|                                                                           |  |                                                             |                                                                                                            | REV<br>D1          |                        |