





P	LTR	DESCRIPTION	DATE	DWN	APVD
B2		REVISED PER ECR-22-162100	23DEC2022	C.C	R.B
C		REVISED PER ECR-23-170031	22MAR2023	C.C	R.B
D		Obsolete 2-1939761-0 2-1939761-4	29APR2024	R.W	R.B




RECOMMEND PC BOARD HOLE PATTERN : CONNECTOR MOUNT SIDE (NOT ACCUMULATE TOLERANCE)  
PC BOARD THICKNESS : 1.0□1.6±0.1



LOGO MARK  
SERIES CODE

CIRCUIT NO KEYING




CAVITY MARK (ALPHABET: CAPITAL LETTER)

RETENTION LEG

HDR CONTACT

HDR HSG

10POS(X-KEY): 1-1939761-0



- △. MATERIAL: HOUSING: GLASS FILED THERMO PLASTIC POLYESTER(94V-0), COLOR: BLACK  
CONTACT: COPPER ALLOY  
RETENTION LEG: PRE-TIN COPPER ALLOY
- △. FINISH (ALL OVER): TIN PLATING 1.0□mMIN  
AFTER NICKEL PLATING 1.27□mMIN.
- 3. THE KEYING ARRANGEMENT OF "Y" IS SYMMETRIC WITH "X".
- 4. THE SHAPE, SIZE AND POSITION OF THE CHARACTER THEY DON'T SHOW DETAILS.

16	Y	15	30.0	33.0	34.6	2-1939761-3
16	X	15	30.0	33.0	34.6	1-1939761-3
14	Y	13	26.0	29.0	30.6	2-1939761-2
14	X	13	26.0	29.0	30.6	1-1939761-2
12	Y	11	22.0	25.0	26.6	2-1939761-1
12	X	11	22.0	25.0	26.6	1-1939761-1
10	Y	9	18.0	21.0	22.6	2-1939761-0
10	X	9	18.0	21.0	22.6	1-1939761-0
8	X	7	14.0	17.0	18.6	2-1939761-8
8	X	7	14.0	17.0	18.6	1-1939761-8
4	Y	3	6.0	9.0	10.6	2-1939761-4
4	X	3	6.0	9.0	10.6	1-1939761-4
POS	KEY	n	A	B	C	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN M. MAEBASHI 30JUL2007  
CHK T. KUDO 30JUL2007  
APVD D. MITSUGI 30JUL2007

DIMENSIONS: mm  
TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.3, ±3°

0 PLC	±
1 PLC	±0.5
2 PLC	±0.13
3 PLC	±0.013
4 PLC	±0.0001
ANGLES	±

MATERIAL FINISH

1 2

PRODUCT SPEC 108-78298  
APPLICATION SPEC 114-5377  
WEIGHT










**TE** TE Connectivity

NAME DYNAMIC D1100S 2.0mm PITCH HDR ASSY (H-TYPE) TIN-PLATE 2-16POS

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-1939761	-

CUSTOMER DRAWING SCALE 4:1 SHEET 1 OF 3 REV D

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1 OF 2			



4POS(X-KEY): I-1939761-4

8POS(X-KEY): I-1939761-8







16POS(X-KEY): I-1939761-3

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. MAEBASHI 30 JUL 2007	<b>STE</b> TE Connectivity
DIMENSIONS: mm		CHK T. KUDO 30 JUL 2007	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D. MITSUGI 30 JUL 2007	NAME DYNAMIC D1100S 2.0mm PITCH HDR ASSY (H-TYPE) TIN-PLATE 2-16POS
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		PRODUCT SPEC 108-78298	SIZE A300779
MATERIAL		APPLICATION SPEC 114-5377	CAGE CODE C-1939761
FINISH		WEIGHT	DRAWING NO C-1939761
		CUSTOMER DRAWING	RESTRICTED TO -
		SCALE 4:1	SHEET 2 OF 3
			REV D

SEE SHEET 1 OF 3


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			



12POS(X-KEY): 1-1939761-1

14POS(X-KEY): 1-1939761-2

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. MAEBASHI 30 JUL 2007	 TE Connectivity NAME DYNAMIC D1100S 2.0mm PITCH HDR ASSY (H-TYPE) TIN-PLATE 2-16POS	RESTRICTED TO -
DIMENSIONS: mm		CHK T. KUDO 30 JUL 2007		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D. MITSUGI 30 JUL 2007		
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		PRODUCT SPEC 108-78298		
MATERIAL		APPLICATION SPEC 114-5377	SIZE A3	CAGE CODE 00779
		WEIGHT	DRAWING NO G-1939761	
CUSTOMER DRAWING			SCALE 4:1	SHEET 3 OF 3
			REV D	

SEE SHEET 1 OF 3