

4

3

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 6-APRIL-2001
 © COPYRIGHT 2001 ALL RIGHTS RESERVED.

SUGGESTED MATING TAB

- MATERIAL:- #2 HARD BRASS OR NICKEL PLATED STEEL.
- NO BURRS PERMISSIBLE AT HOLE.
- TIN PLATING IS REQUIRED ON BRASS WHEN TERMINAL TEMPERATURE IS OVER 85C.

△ MUST BE FLAT WITHIN 0.076 OVER THIS LENGTH.
 5. HOLE MUST BE SYMMETRICAL ABOUT TAB WITHIN 0.076.

2

1

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
IR	-				
B		EBA0-0049-04	25AUG2004	MJG	BB
BI		NOMINAL DIM. CORRECTED AND TOLERANCE ADDED	09JAN2012	PKS	RRP

- CONTINUOUS STRIP ON REELS.
- WIRE SIZE IS 20-16 AWG.
- INSULATION RANGE IS 2.29-3.30 DIA.

△ DIM 5.41mm IN PARALLEL STATE, MAX 6.1mm IN FREE STATE

SECTION D-D

SECTION A-A
SCALE 10:1SECTION B-B
SCALE 10:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.R. TERRY 06APR2001	1337968-1 PART NUMBER	
DIMENSIONS: mm		CHK E. SCOTT 09APR2001	STE TE Connectivity	
TOLERANCES UNLESS OTHERWISE SPECIFIED: LINEAR ±0.5 Ø-PLC ±0.1 1-PLC ±0.1 2-PLC ±0.05 3-PLC ± 4-PLC ± ANGLES ±0.5 FINISH		APVD M. WHELAN 09APR2001	NAME MKI POSITIVE LOCK RECEPTACLE 6.35 (.250) SERIES	
MATERIAL BRASS		PRODUCT SPEC 108-3444 APPLICATION SPEC 114-5029 WEIGHT -	SIZE A20779	RESTRICTED TO -
FINISH TIN		CUSTOMER DRAWING	DRAWING NO C-1337968	SCALE 5:1 SHEET 1 OF 1 REV BI

1471-9 (3/11)

Pro/ENGINEER DRAWING