
THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -,- .
© COPYRIGHT - By - ALL RIGHTS RESERVED.


LOC	DIST
—	—


REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	2	REVISED PER ECO-14-015435	11OCT2014	NK	MM



PCB LAYOUT







1 CURRENT RATING: 6AMP AC300V
OPERATION TEMPERATURE: -40°C TO +150°C
WIRE STRIP LENGTH: 7.5~8.5mm
WIRE RANGE: 14~20AWG

2

MATERIAL			
INSULATING BODY	POLYAMIDE 66		GREEN
COVER	POLYAMIDE 66		GREEN
LEVER	POLYAMIDE 66		ORANGE
TERMINAL	PHOSPHOR BRONZE	TIN PLATED	

△3 CUSTOM BODY COLORS:

	POSITION					
PIN:	1	2	3	4	5	6
3-1986779-4	GREEN	WHITE	BLACK	RED		
3-1986779-6	BROWN	BROWN	PURPLE	GREY	BLUE	RED

PRELIMINARY - NOT RELEASED
FOR PRODUCTION

	A (mm)	NUMBER OF POSITION	PART NUMBER
△3	22.5	6	3-1986779-6
△3	15.5	4	3-1986779-4
	22.5	6	1986779-6
	12.0	3	1986779-3
	8.5	2	1986779-2

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± -
1 PLC ± 0.2
2 PLC ± 0.15
3 PLC ± -
4 PLC ± -
ANGLES ± 2°

MATERIAL -
FINISH -

DWN NAGALAKSHMI K 12FEB2014
CHK MERCURIO, MAURIZIO 12FEB2014
APVD MERCURIO, MAURIZIO 12FEB2014
PRODUCT SPEC —
APPLICATION SPEC —
WEIGHT —

TE Connectivity

NAME TERMINAL BLOCK, PCB MOUNT SCREWLESS, 3.5mm PITCH

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-1986779	—

CUSTOMER DRAWING | SCALE 1:1 | SHEET 1 OF 1 | REV 2

1986779