


P	LTR	DESCRIPTION	DATE	DWN	APVD
	A3	REVISED (ECR-21-125081)	23.DEC.'21	JW	YJ



NOTE

- GENERAL TOLERANCE: ±0.25, ±3°
- APPLICABLE WIRE: AESSX(F) 0.3-0.5sqmm OR EQUIV.
- TE LOGO AND DATE-CODE
- APPLICATOR FEED: 7.0
- MATING TAB THICKNESS: 0.63^{+0/-0.03}
- FOR HIGH VIBRATION APPLICATION
- THE FIRST SPRING IS MARKED WITH AN INDICATION "_____" IN DOUBLE OUT DIES
- THE NUMBER "1" or "2" IS MARKED IN DOUBLE OUT DIES

POS.	DESCRIPTION	FINISH	MATERIAL	PART NUMBER	MARKING	REMARKS
2	SPRING		STAINLESS STEEL	1-2005119-1	H 6	FOR HIGH VIBRATION APPLICATION
1	BODY	PRE-TINNED	COPPER ALLOY			
2	SPRING		STAINLESS STEEL	2005119-1	NONE	
1	BODY	PRE-TINNED	COPPER ALLOY			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SG OH 02-APR-2009	STE TE Connectivity	
DIMENSIONS: mm		CHK YD LEE		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD HG CHO	NAME MQS CLEAN BODY CONTACT	
0 PLC ±		PRODUCT SPEC		
1 PLC ±		APPLICATION SPEC	SIZE A3 CAGE CODE 00779 DRAWING NO C-2005119 RESTRICTED TO -	
2 PLC ±		114-61024		
3 PLC ±		WEIGHT -	SCALE 10:1 SHEET 1 OF 1 REV A3	
4 PLC ±		CUSTOMER DRAWING		
ANGLES ±				
FINISH SEE TABLE				