



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

| LOC | DIST | REVISIONS   |                           |         |       |
|-----|------|-------------|---------------------------|---------|-------|
| P   | LTR  | DESCRIPTION | DATE                      | DWN     | APVD  |
| FT  | 0    | F           | REVISED PER ECO-11-023401 | 01DEC11 | KH MS |



| 1 | DIM S | DIM L | POSN | TE PART NO. |
|---|-------|-------|------|-------------|
| 1 | 7.250 | 7.55  | 30   | 3-1546328-0 |
| 1 | 7.000 | 7.30  | 29   | 2-1546328-9 |
| 1 | 6.750 | 7.05  | 28   | 2-1546328-8 |
| 1 | 6.500 | 6.80  | 27   | 2-1546328-7 |
| 1 | 6.250 | 6.55  | 26   | 2-1546328-6 |
| 1 | 6.000 | 6.30  | 25   | 2-1546328-5 |
| 1 | 5.750 | 6.05  | 24   | 2-1546328-4 |
| 1 | 5.500 | 5.80  | 23   | 2-1546328-3 |
| 1 | 5.250 | 5.55  | 22   | 2-1546328-2 |
| 1 | 5.000 | 5.30  | 21   | 2-1546328-1 |
| 1 | 4.750 | 5.05  | 20   | 2-1546328-0 |
| 1 | 4.500 | 4.80  | 19   | 1-1546328-9 |
| 1 | 4.250 | 4.55  | 18   | 1-1546328-8 |
| 1 | 4.000 | 4.30  | 17   | 1-1546328-7 |
| 1 | 3.750 | 4.05  | 16   | 1-1546328-6 |
| 1 | 3.500 | 3.80  | 15   | 1-1546328-5 |
| 1 | 3.250 | 3.55  | 14   | 1-1546328-4 |
| 1 | 3.000 | 3.30  | 13   | 1-1546328-3 |
| 1 | 2.750 | 3.05  | 12   | 1-1546328-2 |
| 1 | 2.500 | 2.80  | 11   | 1-1546328-1 |
| 1 | 2.250 | 2.55  | 10   | 1-1546328-0 |
| 1 | 2.000 | 2.30  | 9    | 1546328-9   |
| 1 | 1.750 | 2.05  | 8    | 1546328-8   |
| 1 | 1.500 | 1.80  | 7    | 1546328-7   |
| 1 | 1.250 | 1.55  | 6    | 1546328-6   |
| 1 | 1.000 | 1.30  | 5    | 1546328-5   |
| 1 | .750  | 1.05  | 4    | 1546328-4   |
| 1 | .500  | .80   | 3    | 1546328-3   |
| 1 | .250  | .55   | 2    | 1546328-2   |

NOTES:

PHYSICAL PROPERTIES:  
 HOUSING MATERIAL: POLYAMIDE  
 FLAMMABILITY: UL94V-0  
 COLOR: BLACK

TERMINAL:  
 TERMINALS: BRASS, TIN PLATED.  
 SCREWS: M3, STEEL, ZINC PLATED.

MECHANICAL:  
 PITCH (TERMINAL SPACING): .250"  
 RECOMMENDED PCB HOLE DIA.: .073"  
 RECOMMENDED TIGHTENING TORQUE: 10IN-LBS MAX.

ELECTRICAL PROPERTIES:  
 MAXIMUM CURRENT: 10A  
 OPERATING VOLTAGE: 300V  
 WIRE RANGE: 16-30 AWG

ENVIRONMENTAL PROPERTIES:  
 OPERATING TEMP RANGE: -40°C TO 105°C

- 1 PRELIMINARY PART NUMBER.
- 2 SCREWS ARE BOTTOMED.

|  |  |                                   |                            |              |
|--|--|-----------------------------------|----------------------------|--------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT. |  | DWN<br>S SCHLEGEL<br>11JUN02      | <b>STE</b> TE Connectivity |              |
| DIMENSIONS:<br>INCHES                  |  | CHK<br>D.A. BIEVENOUR<br>6/11/02  |                            |              |
| TOLERANCES UNLESS OTHERWISE SPECIFIED: |  | APVD<br>D.A. BIEVENOUR<br>6/11/02 | NAME                       |              |
| 0 PLC ± -                              |  | PRODUCT SPEC                      |                            |              |
| 1 PLC ± -                              |  | APPLICATION SPEC                  |                            |              |
| 2 PLC ± -                              |  | SIZE                              |                            |              |
| 3 PLC ± -                              |  | CAGE CODE                         |                            |              |
| 4 PLC ± -                              |  | DRAWING NO                        |                            |              |
| ANGLES ± -                             |  | RESTRICTED TO                     |                            |              |
| FINISH                                 |  | WEIGHT                            |                            |              |
| -                                      |  | A3 00779 C-1546328                |                            |              |
| -                                      |  | CUSTOMER DRAWING                  |                            |              |
|  |  | SCALE 2:1                         |                            | SHEET 1 OF 1 |
|  |  |                                   |                            | REV F        |