






REVISIONS					
P.	LTR.	DESCRIPTION	DATE	DWN.	APVD.
	A	REVISED PER ECO-14-017984	02DEC2014	AP	DD

- 1 MATERIAL:
HOUSING: LCP, GLASS FILLED, UL94V-0.
TERMINALS: HIGH PERFORMANCE COPPER ALLOY.
- 2 FINISH:
30µ" SELECTIVE GOLD IN CONTACT AREA. SELECTIVE TIN
ON PCB TAILS, NICKEL OVERALL.



SCALE 4:1



RECOMMENDED PCB LAYOUT
MIN BOARD THICKNESS 1.6

REFER TO WWW.TE.COM
FOR PRODUCT AVAILABILITY

NONE		2	2057934-1
KEY POSITION		FINISH	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.		TE Connectivity	
DIMENSIONS:		NAME	
mm		IMPACT, 2 PAIR, DAUGHTERCARD	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		12 COLUMN, UNGUIDED, SIGNAL	
0 PLC ±0.2		MODULE, 0.46 EYELET	
1 PLC ±0.13		SIZE	
2 PLC ±0.13		CAGE CODE	
3 PLC ±0.13		DRAWING NO	
4 PLC ±0.13		RESTRICTED TO	
ANGLES		A100779C=2057934	
FINISH		SCALE	
SEE TABLE		6:1	
MATERIAL		SHEET	
Customer Drawing		1 OF 1	
		REV	
		A	