


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
HG	—		K2	ADD 9-4/9-5	15OCT2014	KZ	RZ



1. LOSS OF CABLE ASSEMBLY $\leq 1.0\text{dB}$ @1310nm & 1550nm
PLUS CABLE ATTENUATION 0.7dB/KM
RETURN LOSS $\geq 50\text{dB}$ @1310nm.


- 2 WHITE MARK ON CONNECTOR BODY INDICATES FIBER 1 SIDE.
3 PRINT THE LABEL AS SHOWN:




- 4 LSZH CABLE SHALL COMPLY WITH THE FOLLOWING REQUIREMENTS:
- FIRE PROPAGATION: IEC 60332-2 OR -1
 - SMOKE EMISSION: IEC 601034
 - ACID GAS EMISSION: IEC 60754
 - TOXICITY: NES 713

PAIRS FLIPPED

FIBER #	COLOR
1	BLUE
2	ORANGE
3	GREEN
4	BROWN
5	SLATE
6	WHITE
7	RED
8	BLACK
9	YELLOW
10	VIOLET
11	ROSE
12	AQUA



VIEW A-A
NOT TO SCALE



VIEW B-B
NOT TO SCALE


FIBER #	COLOR
1	ORANGE
2	BLUE
3	BROWN
4	GREEN
5	WHITE
6	SLATE
7	BLACK
8	RED
9	VIOLET
10	YELLOW
11	AQUA
12	ROSE

LIGHTRAY CONNECTOR FIBER PATH


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SHI BI YUN 10NOV05	TE Connectivity			
DIMENSIONS: METER		CHK ALLEN GUMP 10NOV05				
		APVD RICHARD ZHAO 10NOV05	NAME MTP TO MTP TRUNK OS2 12F LSZH P/FLIPPED			
		PRODUCT SPEC	-			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	-			
MATERIAL		WEIGHT	SIZE A2	CAGE CODE 00779	DRAWING NO 1568683	RESTRICTED TO
FINISH		CUSTOMER DRAWING	SCALE NTS	SHEET 1 of 2	REV K2	

LOC	DIST	REVISIONS			
HG	—	P	LTR	DESCRIPTION	DATE
		—		SEE SHEET 1	—

PART NUMBER	L (METER)	
	MIN	MAX
0-1568683-1	10.00	10.20
0-1568683-2	20.00	20.40
0-1568683-3	30.00	30.60
0-1568683-4	40.00	40.80
0-1568683-5	50.00	51.00
0-1568683-6	60.00	61.20
0-1568683-7	70.00	71.40
0-1568683-8	80.00	82.40
0-1568683-9	90.00	92.70
1-1568683-0	100.00	103.00
1-1568683-1	110.00	115.50
1-1568683-2	120.00	126.00
1-1568683-3	130.00	136.50
1-1568683-4	140.00	147.00
1-1568683-5	150.00	157.50
1-1568683-6	160.00	168.00
1-1568683-7	170.00	178.50
1-1568683-8	180.00	189.00
1-1568683-9	190.00	199.50
2-1568683-0	200.00	210.00
2-1568683-1	210.00	220.50
2-1568683-2	220.00	231.00
2-1568683-3	230.00	241.50
2-1568683-4	240.00	252.00
2-1568683-5	250.00	262.50
2-1568683-6	260.00	273.00
2-1568683-7	270.00	283.50
2-1568683-8	280.00	294.00
2-1568683-9	290.00	304.50
3-1568683-0	300.00	315.00
4-1568683-0	5.00	5.20
4-1568683-1	15.00	15.30
4-1568683-2	25.00	25.50
4-1568683-3	35.00	35.70
4-1568683-4	45.00	45.90
9-1568683-1	70.00	71.00
9-1568683-2	30.00	30.30
9-1568683-3	40.00	40.40
9-1568683-4	20.00	20.20
9-1568683-5	60.00	60.60



PROTECTIVE COVER
BOTTOM END



PULLING SOCK
TOP END

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SHI BI YUN 10NOV05		 TE Connectivity	
		CHK ALLEN GUMP 10NOV05			
DIMENSIONS: METER		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME MTP TO MTP TRUNK OS2 12F LSZH P/FLIPPED	
		APVD RICHARD ZHAO 10NOV05			
		PRODUCT SPEC —			
		APPLICATION SPEC —			
		SIZE A2			
		CAGE CODE 00779			
MATERIAL —		FINISH —		DRAWING NO C=1568683	
		WEIGHT —		RESTRICTED TO —	
		CUSTOMER DRAWING		SCALE NTS	
				SHEET 2 OF 2	
				REV K2	