

4

3

2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
H3		REVISED PER ECO-11-004587	11MAR11	RK	HMR
J		REVISED PER ECR-16-017870	20APR2017	BDA	MZ

1.125±.025
 .844±.010
 1.25±.025
 .844±.010
 FLANGED
 A HOLE
 4 PLC

.809 MAX
 .420±.015
 .094±.010
 5/8-24 UNEF-2A
 Ø.688±.010
 Ø.630 MAX
 .125 MAX
 PANEL THK

.844±.010
 Ø.840
 .844±.010
 Ø.125 ^{+0.007}/_{-0.000}
 4 PLC

RECOMMENDED PANEL CUTOUT
 SCALE 2:1

Ø.935 MAX
 .817 MAX
 FREE HANGING

STANDARD	YES	4-40 BRASS THREADED INSERT	20	FLANGED	△5 206433-6
SMALL PACK	NO	.125 DIA	20	FLANGED	206433-5
STANDARD	NO	.125 DIA	20DF WITHOUT INSULATION SUPPORT	FLANGED	△5 206433-4
STANDARD	NO	4-40 BRASS THREADED INSERT	20	FLANGED	206433-3
STANDARD	NO	-	20	FREE HANGING	206433-2
STANDARD	NO	.125 DIA	20	FLANGED	206433-1
PACKAGING	PERIPHERAL SEAL	A	WILL ACCEPT SOCKET CONTACT SIZE	TYPE	PART NUMBER

1 CONTACT CAVITIES IDENTIFIED BY CHARACTERS ON FRONT AND REAR FACE.
 △2 AMP MOLDED ON THIS SURFACE.
 △3 PART NUMBER AND DATE CODE MARKED ON THIS SURFACE.
 4 206433-4 STRIPPED WIRE LENGTH SHOULD BE .193-.213 WITH .095 MAX INSULATION.
 △5 OBSOLETE PART NUMBER.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DWN J.McCLINTON 1-25-88	 TE Connectivity RECEPTACLE ASSEMBLY, ARRANGEMENT 11-8 REVERSE SEX, CPC
	0 PLC ± -	CHK R.STONE 1-26-88	
	1 PLC ± -	APVD M.KAPEZYNSKI 1-27-88	
	2 PLC ± -	PRODUCT SPEC	
	3 PLC ± .005	APPLICATION SPEC	SIZE A2
	4 PLC ± -	WEIGHT	CAGE CODE 00779
	ANGLES ± -	CUSTOMER DRAWING	DRAWING NO C=206433
MATERIAL NYLON, GLASS FILLED, FLAME RETARDED, BLACK	FINISH -	SCALE 4:1	RESTRICTED TO -
		SHEET 1 of 1	REV J

1471-9 (1/15)

206433