

4

3

2

1


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
© COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD		
	A	RELEASE PER ECR-15-000195	09JAN15	SW	RZ		

PART NUMBER
2064873-1

NOTES:

1. MAXIMUM INSERTION LOSS IS 0.5 dB AT 850 & 1300nm.
2. MINIMUM RETURN LOSS: 20dB AT 850 & 1300nm
3. INCLUDE IL & RL TEST DATA WITH EACH LOOPBACK
4. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TE STANDARD TEC-138-702.



2064873

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SIMON WU 16OCT12	STE TE Connectivity	
		CHK KIM ZHANG 16OCT12		
DIMENSIONS: mm		APVD RICHARD ZHAO 16OCT12	NAME CABLE ASSY, FIBER OPTIC, MM 62.5/125 LC DUPLEX LOOPBACK	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	RESTRICTED TO	
0 PLC ± -		APPLICATION SPEC	SIZE A2	CAGE CODE 00779
1 PLC ± -		WEIGHT	DRAWING NO C-2064873	REV A
2 PLC ± -		CUSTOMER DRAWING		
3 PLC ± -		SCALE NTS		
4 PLC ± -		SHEET 1 OF 1		
ANGLES ± -				
FINISH -				