

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	E1	ECR-20-004655	06OCT20	RK	SBH

NOTE:


1. PACKAGING ACC. TO TE SPEC.107-18032 BUNDLE EVERY 25 ASSEMBLIES WITH A RUBBER BAND
2. ELECTRICAL TEST CONTAINING "SHORT CIRCUIT TEST, CONTINUITY AND ACCURATE CAVITY ASSIGNMENT TEST" ACC. TO TE-SPEC.108-18857, SUBSECTION 3.1.1
3. ASSEMBLY COLOR: WHITE

KEYING ACC. TO TABLE

4

PN	KEYING
1--X	HV-3
2--X	LV-2

	PN	L	TOLERANCES/mm
	X-2083073-1	610mm (2ft)	+/- 5
OBSOLETE	X-2083073-2	1270mm (4ft)	+/- 15
	X-2083073-3	1880mm (6ft)	+/- 20
	X-2083073-4	2490mm (8ft)	+/- 20
OBSOLETE	X-2083073-5	3100mm (10ft)	+/- 30
	X-2083073-6	3660mm (12ft)	+/- 30
	X-2083073-7	4270mm (14ft)	+/- 50
	X-2083073-8	4880mm (16ft)	+/- 50



UOM	QTY	QTY	DESCRIPTION	POS.
mm	AR	AR	Cable SVT 2xAWG18 UL WH	6
PC	-	1	PLUG MINI HVL HV-3	5
mm	1	-	PLUG MINI HVL LV-2	
PC	2	2	MICRO QUADLOK SYSTEM SOCKET CONTACT	4
PC	2	2	TUBE FOR SVT CABLE	3
PC	2	2	MICRO QUADLOK SYSTEM PIN CONTACT	2
PC	-	1	OUTLET, MINI HVL 7.5mm HV-3	1
PC	1	-	OUTLET, MINI HVL 7.5mm LV-2	
	2--X	1--X		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAVINDRA K 28MAR11	STE TE Connectivity		
DIMENSIONS: mm		CHK R.HOSSAINI 31MAR11			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD R.HOSSAINI 31MAR11	NAME CABLE ASSEMBLY NECTOR S LINE 2POS. HV-3 AND LV-2		
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC -	APPLICATION SPEC -		
MATERIAL -		FINISH -	WEIGHT -	SIZE A3	CAGE CODE 00779
CUSTOMER DRAWING			DRAWING NO C-2083073	RESTRICTED TO -	
			SCALE NTS	SHEET 1 OF 1	REV E1