






LOC		DIST		REVISIONS			
AF	50	REV	DATE	BY	APPV	DATE	DESCRIPTION
A1		REVISED PER	14MAY13	KH	GJ		ECR-13-007757

- SPECIFICATION: WIRE RANGE; #18-#34 AWG. 0.16-1.02 mm [.006-.040] DIA. COPPER MAGNET WIRE.
- POCKET RECOMMENDATION: 1601424
- TERMINAL APPLICATION TO COMPLY WITH TYCO ELECTRONICS SPEC 114-13166, CONSULT TYCO ELECTRONICS PRODUCT ENGINEERING FOR PROPER INSERTION DEPTH.
- TAB TO BE SELECTIVE POST PLATED 1.0-3.0 MICRONS SILVER PER ASTM B700 (98% PURE MIN) TO INCLUDE TARNISH RESIST. SILVER PLATING MAY EXTEND ONTO CARRIER. ENTIRE TERMINAL TO BE 0.5-0.2 MICRONS NICKEL PLATED PER ASTM B689.
- 2 TERMINALS SHOWN FOR ILLUSTRATION PURPOSES.



1601261-2
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DRN: JR_RUTH 28JAN11	TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK: G. JACONO 28JAN11	NAME: STANDARD RANGE WIRE TO 4.52 [.178] X 0.51 [.020], OFFSET TAB SIAMEZE TERMINAL.	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPV: G. JACONO 28JAN11	PRODUCT SPEC: 108-2085	
0 PLC ± -		APPLICATION SPEC: 3		
1 PLC ± -		SIZE: A1		
2 PLC ± 0.13 [.005]		CAGE CODE: 00779		
3 PLC ± -		DRAWING NO: 1601261		
4 PLC ± -		RESTRICTED TO: -		
ANGLES ± °		CUSTOMER DRAWING		
MATERIAL: FULL HARD BRASS	FINISH: 4	WEIGHT: -	SCALE: 11:1	SHEET 1 OF 1 REV A1