

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY TYCO ELECTRONICS CORPORATION

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A3	ECO-14-004886	31MAR2014	DR	DR
	B	ECN-22-186318	23NOV2022	SS	PK
	B1	ECN-23-192905	07JAN2023	SS	PK

Top view of the cable seal showing a central circular opening with a diameter dimension of $2X \text{ } \varnothing D \pm 0.20$. The seal has a rounded rectangular outer shape with a radius dimension of $R6.00 \pm 0.20$. There are four small circular features around the central opening. The material is labeled as VMQ.

Side view of the cable seal showing a height dimension of 17.00 ± 0.20 . The seal has a multi-ribbed profile.

Isometric view of the cable seal showing its three-dimensional shape.

SCALE 2:1

Section A-A of the cable seal showing a cross-section with a height dimension of 5.80 ± 0.20 and a width dimension of $2X 25.10 \pm 0.20$. The central opening has a diameter dimension of $2X \text{ } \varnothing D \pm 0.20$.

SECTION A-A

1. NO DAMAGES, SINK MARKS, CAVITIES AND FLOW LINES PERMITTED
2. MATERIAL: 30 DUROMETER INHERENTLY LUBRICATED SILICONE
COLOR: SEE TABLE
3. AROUND NO FLASH PERMITTED
4. NOTE DELETED

7.70	1.86 g	PURPLE	9.30-10.10	B	2103154-3
8.50	1.79 g	RED	9.80-10.50	B	2103154-2
9.80	1.63 g	YELLOW	10.70-11.40	B	2103154-1
D	WEIGHT	COLOR	CABLE DIAMETER	REV	PART NO

B

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPROVALS		TE Connectivity	
mm		0 PLC	±	DWN	D. RHEIN	16MAR2011	
		1 PLC	±0.2	CHK	D. RHEIN	16MAR2011	
		2 PLC	±0.16	APVD	J. BOLEWITZ	16MAR2011	
		3 PLC	±	PRODUCT SPEC		NAME	
		4 PLC	±	APPLICATION SPEC		CABLE SEAL	
		ANGLES	±2°	WEIGHT		HVA280 MULTI-CORE	
MATERIAL		FINISH		SIZE		CAGE CODE	
2				A3		00779	
				DRAWING NO		G-2103154	
				CUSTOMER DRAWING		RESTRICTED TO	
				SCALE		SHEET	
				4:1		1 OF 1	
				REV		B1	

1470-19 (3/13)