



D


C

B


A



KEY POSITION CHART			
NONE			
A	F		
B	E		
C	G		
D	H		



RECOMMENDED PCB LAYOUT
MIN BOARD THICKNESS 1.0



- 1

MATERIAL:


HOUSING: LCP, GLASS FILLED, UL94V-0.

TERMINALS: HIGH PERFORMANCE COPPER ALLOY.
- 2

FINISH:

30µ" SELECTIVE GOLD IN CONTACT AREA. SELECTIVE TIN ON PCB TAILS, NICKEL OVERALL.
- 3

CONNECTORS SUPPLIED WITH MOUNTING SCREWS.



SCALE 4:1

REFER TO WWW.TE.COM
FOR PRODUCT AVAILABILITY

H	2	8-2132761-1
G	2	7-2132761-1
F	2	6-2132761-1
E	2	5-2132761-1
D	2	4-2132761-1
C	2	3-2132761-1
B	2	2-2132761-1
A	2	1-2132761-1
NONE	2	2132761-1
KEY POSITION	FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN - 31MAR2011		
		CHK D. DIXON 31MAR2011		
DIMENSIONS:		APVD D. DIXON 31MAR2011	NAME	
mm		PRODUCT SPEC	IMPACT, 6 PAIR, DAUGHTERCARD 6 COLUMN, RIGHT GUIDED, SIGNAL MODULE, 0.46 EYELET	
		APPLICATION SPEC		
MATERIAL		SIZE	CAGE CODE	DRAWING NO
		WEIGHT	-	A100779C=2132761
		Customer Drawing	SCALE 5:1	SHEET 1 OF 1 REV C