



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
FX	00	B4	REVISED PER ECO-12-012319	03JUL2012	DD TB
		B5	REVISED PER ECO-13-010333	20JUN2013	DD TB
		C	REVISED PER ECO-13-010454	28JUN2013	DD TB



1. 8.4mm² conductor. Current rating depends upon conductor size. Keep terminals below 150°C maximum continuous.
2. 3 minutes @ +40°C ambient with 8.4mm² (#8AWG) conductor.
3. A coil economizer circuit is needed if coil is energized for an extended length of time at a high operating temperature (i.e. 85°C).



2138168-1
 TE PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. DRUMMOND 21OCT2011	TE Connectivity	
DIMENSIONS: INCHES [mm]		CHK T. BLACKMON 21OCT2011		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD T. BLACKMON 21OCT2011	NAME RELAY, EVC135 SIDE MOUNT (15.3 OHM COIL)	
0 PLC ± 1 PLC ±0.1 2 PLC ±0.01 3 PLC ± 4 PLC ± ANGLES ±° FINISH		PRODUCT SPEC -	SIZE A200779	DRAWING NO C-2138168-1
MATERIAL -		APPLICATION SPEC -	RESTRICTED TO -	SCALE 2:1
		WEIGHT -	SHEET 1	OF 1
		Customer Drawing	REV C	