



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
J	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
		A		REVISED ECR-08-002970	06MAR2008	Y.Y	D.M



- JUMPER LENGTH "L" IS FROM 12.7 MIN. TO 609.6 MAX.
- RECOMMENDED THROUGH HOLE DIA DIMENSION FOR P.C.BOARD: $\phi 0.71 \pm 0.025$
THROUGH HOLE PITCH TOLERANCE: ± 0.127
- ANOTHER SPECIFICATION SHOULD BE ESTABLISHED IN CASE OF DEVIATION FROM THIS SPECIFICATION.
- WHEN N IS GREATER THAN 31, PCN INSERTION IS SUBJECT TO HAVE DIFFICULTY.
- DIMENSIONS OF LEAD POSITION ARE FOOT OF LEAD.

2	12.7	5	-	NOT AVAILABLE	-
			-	NOT AVAILABLE	-
			-	NOT AVAILABLE	-
			-	NOT AVAILABLE	-
			FS2A12.7A5=JUMPER	1717404-1	A
P	L	N	PART NAME	PN	TYPE

- ジャンパー長さ"L"は、最小12.7から、最大609.6まで。
- プリント基板スルーホール径： $\phi 0.71 \pm 0.025$ また、スルーホールピッチ公差は、 ± 0.127 である。(推奨)
- 本仕様から逸脱する場合は、必ず仕様打合わせを行うこと。
- N31以上製品は、プリント基板挿入性が悪い場合がある。
- リード位置寸法は、リード根元部寸法とする。

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN D.MITSUGI 28MAY03
 CHK S.MANABE 28MAY03
 APVD S.MANABE 28MAY03

PRODUCT SPEC 製品規格
 108-78018

APPLICATION SPEC 取付適用規格

WEIGHT 0.1 g

SIZE A3 CAGE CODE 00779 DRAWING NO 1717404 RESTRICTED TO

CUSTOMER DRAWING SCALE 尺度 SHEET 1 of 1 REV A

Tyco Electronics Corporation
 Kawasaki, Japan

HI FLEX JUMPER P2L12.7A5