



© 2019 TE Connectivity. All Rights Reserved.

THE DRAWING SHOWS THE 2-DIMENSIONAL REFERENCE COMPONENT CONDITION OF THE ASSEMBLY TO IDENTIFY AND SPECIFY THE NECESSARY DIMENSIONS ONLY. THE DELIVERED PARTS MAY DEVIATE FROM THE DRAWING REGARDING THE ORIENTATION AND POSITION OF EACH COMPONENT (e.g. SLACK CABLE), SO FAR THE FUNCTIONALITY IS NOT CONCERNED.

DIE ZEICHNUNG ZEIGT DEN 2-DIMENSIONALEN IDEALZUSTAND DES ZUSAMMENBAUTEILS BEZÜGLICH DER KOMPONENTEN ZUR IDENTIFIKATION UND SPEZIFIKATION DER NOTWENDIGEN DIMENSIONEN. HINSICHTLICH DER ORIENTIERUNG UND DER LAGE DER KOMPONENTEN (z.B. BIEGESCHLAFES KABEL) KOENNEN DIE GELIEFERTEN TEILE VON DER ZEICHNUNG ABWEICHEN, SOFERN DIE FUNKTIONALITAET NICHT BEEINTRAECHTIGT IST.

REVISIONS ÄNDERUNGEN					
P	LTR	DESCRIPTION BESCHREIBUNG	DATE	DWN	APVD
	H1	PACKAGING UPDATED	07MAR2018	OS	OB
	H2	SC/CC SYMBOLS UPDATED	14MAY2019	OS	VV
	H3	NOTES UPDATED	31MAY2019	OS	VV
	J	SUBCOMPONENT CHANGED, NOTES UPDATED	16JUN2023	OS	PS



LENGTH SCHEDULE:

TE PART NO.	REV.	LENGTH L (mm)	TOL.	FORD PART NO.	RELEASE NO.	ALERT NO.
2141730-1	E	521	+30	BU4T-18812-SC	-	-
2141730-4	E	791	+30	BU4T-18812-WC	-	-

NOTES

- 1 PACKAGING:
ASSEMBLIES PACKED IN TE STANDARD BOXES
ACC. TO TE SPECIFICATION 107-18087, 107-18064.
- 2 ELECTRICAL TEST ACC. TO SPECIFICATION 108-18857:
3.1.1 STANDARD CHECK ITEM: A (MAX. 1 OHM, TESTING WITH 5 V DC),
B (MIN. 1 KOHM, TESTING WITH 5 V DC), C, D.
3.1.2 SPECIAL CHECK ITEM: A (MIN. 100 MOHM, TESTING WITH 1000 V), D, N.
- 3 APPLICATION SPECIFICATION FOR FAKRA IV CONNECTOR SYSTEM IS 114-13157,
CRIMP HEIGHT OF CENTRE CONTACT AND FERRULE
ACCORDING APPLICATION SPECIFICATION.
- 4 LABEL TO BE APPLIED AFTER SUCCESSFUL ELECTRICAL TEST:
PRODUCTION DATE: YEAR, MONTH, DAY, SHIFT (YYYYMMDD),
PRODUCTION LOCATION: 5 LETTER CODE OF THE PRODUCTION PLANT,
BARCODE - TYPE 128B: FORD PN,
2D CODE (DATAMATRIX): ACC. PRODUCTION PLANT REQUIREMENTS.
- 5 ALTERNATIVELY THE RTK 031 COAX CABLE PN 956339-3
CAN BE USED INSTEAD OF RTK 031 COAX CABLE PN 956339-2.

-	-	956339-2	COAX CABLE RTK 031 BIS 105 GRAD	8
2	2	2203232-2	SOCKET CONTACT, PLUG, 180 DEGREE, SMB	7
1	1	4-1768418-0	LABEL	6
1	1	1557159-1	CLIP FOR FAKRA HOUSING, FIXED	5
2	2	1488167-1	FERRULE, RTK031, 180 GRAD	4
2	2	2098285-1	PLUG SUBASSEMBLY, RTK031, FAKRA	3
1	1	1438894-2	1 POS. LOCK WITH BODY CLIP	2
1	1	2138710-1	1 POS.PLUG HOUSING,180 DEGREE.CODE A	1
QTY - 4	QTY - 1	PART NO.	DESCRIPTION	ITEM NO.
WEIGHT OF ASSY NO. [g]				

DIESE ZEICHNUNG IST EIN KONTROLLIERTES DOKUMENT. BEMASSUNGEN UND TOLERANZEN GEMAESS GPS (ISO STANDARDS).
TOLERANCING EN ISO 8015
TOLERIERUNG EN ISO 8015

THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER GPS (ISO STANDARDS).

DIMENSIONS: MASSEINHEITEN: (MM)	TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLGEMEINTOLERANZEN	DWN O. Snajder 14DEC2010	
	0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES/W INKEL ±	CHK P. Skrovaneck 14DEC2010	
MATERIAL	FINISH/OBERFLAECHE/FARBE	APVD R. Hort 17DEC2010	

NAME: FAKRA, RTK 031 CABLE ASSEMBLY



SIZE: A3 CAGE CODE: 00779 DRAWING NO: 2141730 RESTRICTED TO NUR FUER

CUSTOMER DRAWING /KUNDENZEICHNUNG SCALE MASSSTAB 1:1 SHEET BLATT 1 OF VON 5 REV J

THE DRAWING SHOWS THE 2-DIMENSIONAL REFERENCE COMPONENT CONDITION OF THE ASSEMBLY TO IDENTIFY AND SPECIFY THE NECESSARY DIMENSIONS ONLY. THE DELIVERED PARTS MAY DEVIATE FROM THE DRAWING REGARDING THE ORIENTATION AND POSITION OF EACH COMPONENT (e.g. SLACK CABLE), SO FAR THE FUNCTIONALITY IS NOT CONCERNED.

DIE ZEICHNUNG ZEIGT DEN 2-DIMENSIONALEN IDEALZUSTAND DES ZUSAMMENBAUTEILS BEZUEGLICH DER KOMPONENTEN ZUR IDENTIFIKATION UND SPEZIFIKATION DER NOTWENDIGEN DIMENSIONEN. HINSICHTLICH DER ORIENTIERUNG UND DER LAGE DER KOMPONENTEN (z.B. BIEGESCHLAFES KABEL) KOENNEN DIE GELIEFERTEN TEILE VON DER ZEICHNUNG ABWEICHEN, SOFERN DIE FUNKTIONALITAET NICHT BEEINTRAECHTIGT IST.

REVISIONS ÄNDERUNGEN					
P	LTR	DESCRIPTION BESCHREIBUNG	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



LENGTH SCHEDULE:

TE PART NO.	REV.	LENGTH L (mm)	TOL.	FORD PART NO.	RELEASE NO.	ALERT NO.
2141730-2	G	830	+30	BU4T-18812-TA	-	-

NOTES

- 1 PACKAGING:
ASSEMBLIES PACKED IN TE STANDARD BOXES ACC. TO TE SPECIFICATION 107-18087, 107-18064.
- 2 ELECTRICAL TEST ACC. TO SPECIFICATION 108-18857:
3.1.1 STANDARD CHECK ITEM: A (MAX. 1 OHM, TESTING WITH 5 V DC), B (MIN. 1 KOHM, TESTING WITH 5 V DC), C, D.
3.1.2 SPECIAL CHECK ITEM: A (MIN. 100 MOHM, TESTING WITH 1000 V), D, N.
- 3 APPLICATION SPECIFICATION FOR FAKRA IV CONNECTOR SYSTEM IS 114-13157, CRIMP HEIGHT OF CENTRE CONTACT AND FERRULE ACCORDING APPLICATION SPECIFICATION.
PULL OUT FORCE OF CENTRE CONTACT MIN. 50 N.
- 4 LABEL TO BE APPLIED AFTER SUCCESSFUL ELECTRICAL TEST:
PRODUCTION DATE: YEAR, MONTH, DAY, SHIFT (YYYYMMDDS),
PRODUCTION LOCATION: 5 LETTER CODE OF THE PRODUCTION PLANT,
BARCODE - TYPE 128B: FORD PN,
2D CODE (DATAMATRIX): ACC. PRODUCTION PLANT REQUIREMENTS.
- 5 ALTERNATIVELY THE RTK 031 COAX CABLE PN 956339-3 CAN BE USED INSTEAD OF RTK 031 COAX CABLE PN 956339-2.

QTY	PART NO.	DESCRIPTION	ITEM NO.
-	956339-2	COAX CABLE RTK 031 BIS 105 GRAD	12
1	2365471-2	SOCKET CONTACT, PLUG, 180 DEGREE, SMB	11
1	2365466-7	PIN CONTACT, JACK, 180 DEGREE, SMB	10
1	4-1768418-0	LABEL	9
1	1438888-1	1 POS. LOCK, 180 DEGREE, FAKRA	8
1	2203238-1	PLUG SUBASSEMBLY, RTK031, FAKRA	7
1	1438893-2	1 POS. PLUG HOUSING, 180 DEGREE, CODE B	6
1	1557159-1	CLIP FOR FAKRA HOUSING, FIXED	5
2	1488167-1	FERRULE, RTK031, 180 GRAD	4
1	1438894-2	1 POS. LOCK WITH BODY CLIP	3
1	2203241-1	JACK SUBASSEMBLY, RTK031, FAKRA	2
1	1438887-2	1 POS. JACK HOUSING, 180 DEGREE, CODE B	1
-		WEIGHT OF ASSY NO. [g]	

DIESE ZEICHNUNG IST EIN KONTROLLIERTES DOKUMENT. BEMESSUNGEN UND TOLERANZEN GEMAESS GPS (ISO STANDARDS).		TOLERANCING EN ISO 8015 TOLERIERUNG EN ISO 8015																					
THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER GPS (ISO STANDARDS).		DWN 14DEC2010 O. Snajder CHK 14DEC2010 P. Skrovanek APVD 17DEC2010 R. Hort																					
DIMENSIONS: MASSEINHEITEN: (MM)		TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLGEMEINTOLERANZEN																					
<table border="1"> <tr><td>0 PLC</td><td>±</td></tr> <tr><td>1 PLC</td><td>±</td></tr> <tr><td>2 PLC</td><td>±</td></tr> <tr><td>3 PLC</td><td>±</td></tr> <tr><td>4 PLC</td><td>±</td></tr> <tr><td>ANGLES/WINKEL</td><td>±</td></tr> </table>		0 PLC	±	1 PLC	±	2 PLC	±	3 PLC	±	4 PLC	±	ANGLES/WINKEL	±	<table border="1"> <tr><td>PRODUCT SPEC</td><td>-</td></tr> <tr><td>PRODUKTSPEZ.</td><td>-</td></tr> <tr><td>APPLICATION SPEC</td><td>-</td></tr> <tr><td>VERARBEITUNGSSPEZ.</td><td>-</td></tr> </table>		PRODUCT SPEC	-	PRODUKTSPEZ.	-	APPLICATION SPEC	-	VERARBEITUNGSSPEZ.	-
0 PLC	±																						
1 PLC	±																						
2 PLC	±																						
3 PLC	±																						
4 PLC	±																						
ANGLES/WINKEL	±																						
PRODUCT SPEC	-																						
PRODUKTSPEZ.	-																						
APPLICATION SPEC	-																						
VERARBEITUNGSSPEZ.	-																						
MATERIAL		WEIGHT GEWICHT																					
-		-																					
-		-																					
CUSTOMER DRAWING		/KUNDENZEICHNUNG																					
SCALE MASSSTAB 1:1		SHEET BLATT 2 OF VON 5																					
DRAWING NO. ZEICHNUNGS-NR. G=2141730		RESTRICTED TO NUR FUER -																					
SIZE A3		CAGE CODE 00779																					





NAME
FAKRA, RTK 031
CABLE ASSEMBLY

© 2019 TE Connectivity. All Rights Reserved.

THE DRAWING SHOWS THE 2-DIMENSIONAL REFERENCE COMPONENT CONDITION OF THE ASSEMBLY TO IDENTIFY AND SPECIFY THE NECESSARY DIMENSIONS ONLY. THE DELIVERED PARTS MAY DEVIATE FROM THE DRAWING REGARDING THE ORIENTATION AND POSITION OF EACH COMPONENT (e.g. SLACK CABLE), SO FAR THE FUNCTIONALITY IS NOT CONCERNED.

DIE ZEICHNUNG ZEIGT DEN 2-DIMENSIONALEN IDEALZUSTAND DES ZUSAMMENBAUTEILS BEZUEGLICH DER KOMPONENTEN ZUR IDENTIFIKATION UND SPEZIFIKATION DER NOTWENDIGEN DIMENSIONEN. HINSICHTLICH DER ORIENTIERUNG UND DER LAGE DER KOMPONENTEN (z.B. BIEGESCHLAFTES KABEL) KOENNEN DIE GELIEFERTEN TEILE VON DER ZEICHNUNG ABWEICHEN, SOFERN DIE FUNKTIONALITAET NICHT BEEINTRAECHTIGT IST.

REVISIONS ÄNDERUNGEN					
P	LTR	DESCRIPTION BESCHREIBUNG	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



LENGTH SCHEDULE:

TE PART NO.	REV.	LENGTH L (mm)	TOL.	FORD PART NO.	RELEASE NO.	ALERT NO.
2141730-3	D	535	+30	BU4T-18812-VB	-	-
2141730-6	D	770	+30	BU4T-18812-YB	-	-

QTY	QTY	PART NO.	DESCRIPTION	ITEM NO.
-	-	956339-2	COAX CABLE RTK 031 BIS 105 GRAD	11
1	1	2365471-2	SOCKET CONTACT, PLUG, 180 DEGREE, SMB	10
1	1	2365466-7	PIN CONTACT, JACK, 180 DEGREE, SMB	9
1	1	4-1768418-0	LABEL	8
1	1	2203238-1	PLUG SUBASSEMBLY, RTK031, FAKRA	7
1	1	1438893-3	1 POS. PLUG HOUSING, 180 DEGREE, CODE C	6
2	2	1557159-1	CLIP FOR FAKRA HOUSING, FIXED	5
2	2	1488167-1	FERRULE, RTK031, 180 GRAD	4
2	2	1438894-2	1 POS. LOCK WITH BODY CLIP	3
1	1	2203241-1	JACK SUBASSEMBLY, RTK031, FAKRA	2
1	1	1438887-3	1 POS. JACK HOUSING, 180 DEGREE, CODE C	1
QTY - 6		WEIGHT OF ASSY NO. [g]		
QTY - 3				

NOTES

- 1 PACKAGING:
ASSEMBLIES PACKED IN TE STANDARD BOXES ACC. TO TE SPECIFICATION 107-18087, 107-18064.
- 2 ELECTRICAL TEST ACC. TO SPECIFICATION 108-18857:
3.1.1 STANDARD CHECK ITEM: A (MAX. 1 OHM, TESTING WITH 5 V DC), B (MIN. 1 KOHM, TESTING WITH 5 V DC), C, D.
3.1.2 SPECIAL CHECK ITEM: A (MIN. 100 MOHM, TESTING WITH 1000 V), D, N.
- 3 APPLICATION SPECIFICATION FOR FAKRA IV CONNECTOR SYSTEM IS 114-13157, CRIMP HEIGHT OF CENTRE CONTACT AND FERRULE ACCORDING APPLICATION SPECIFICATION.
PULL OUT FORCE OF CENTRE CONTACT MIN. 50 N.
- 4 LABEL TO BE APPLIED AFTER SUCCESSFUL ELECTRICAL TEST:
PRODUCTION DATE: YEAR, MONTH, DAY, SHIFT (YYYYMMDD),
PRODUCTION LOCATION: 5 LETTER CODE OF THE PRODUCTION PLANT,
BARCODE - TYPE 128B: FORD PN,
2D CODE (DATAMATRIX): ACC. PRODUCTION PLANT REQUIREMENTS.
- 5 ALTERNATIVELY THE RTK 031 COAX CABLE PN 956339-3 CAN BE USED INSTEAD OF RTK 031 COAX CABLE PN 956339-2.

DIESE ZEICHNUNG IST EIN KONTROLLIERTES DOKUMENT. BEMASSUNGEN UND TOLERANZEN GEMAESS GPS (ISO STANDARDS).

THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER GPS (ISO STANDARDS).



DIMENSIONS: MASSEINHEITEN: (MM)	TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLGEMEINTOLERANZEN	DWN 14DEC2010 O. Snajder	TOLERANCING EN ISO 8015 TOLERIERUNG EN ISO 8015
	0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES/WINKEL ±	CHK 14DEC2010 P. Skrovaneck	TE Connectivity NAME FAKRA, RTK 031 CABLE ASSEMBLY
MATERIAL	FINISH/OBERFLAECHE/FARBE	APVD 17DEC2010 R. Hort	
		PRODUCT SPEC PRODUKTSPEZ.	SIZE A3 CAGE CODE 00779 DRAWING NO. ZEICHNUNGS-NR. C=2141730
		APPLICATION SPEC VERARBEITUNGSSPEZ.	RESTRICTED TO NUR FUER
		WEIGHT GEWICHT	CUSTOMER DRAWING /KUNDENZEICHNUNG SCALE MASSSTAB 1:1 SHEET BLATT 3 OF VON 5 REV J

© 2019 TE Connectivity. All Rights Reserved.

THE DRAWING SHOWS THE 2-DIMENSIONAL REFERENCE COMPONENT CONDITION OF THE ASSEMBLY TO IDENTIFY AND SPECIFY THE NECESSARY DIMENSIONS ONLY. THE DELIVERED PARTS MAY DEVIATE FROM THE DRAWING REGARDING THE ORIENTATION AND POSITION OF EACH COMPONENT (e.g. SLACK CABLE), SO FAR THE FUNCTIONALITY IS NOT CONCERNED.

DIE ZEICHNUNG ZEIGT DEN 2-DIMENSIONALEN IDEALZUSTAND DES ZUSAMMENBAUTEILS BEZUEGLICH DER KOMPONENTEN ZUR IDENTIFIKATION UND SPEZIFIKATION DER NOTWENDIGEN DIMENSIONEN. HINSICHTLICH DER ORIENTIERUNG UND DER LAGE DER KOMPONENTEN (z.B. BIEGESCHLAFES KABEL) KOENNEN DIE GELIEFERTEN TEILE VON DER ZEICHNUNG ABWEICHEN, SOFERN DIE FUNKTIONALITAET NICHT BEEINTRAECHTIGT IST.

REVISIONS ÄNDERUNGEN					
P	LTR	DESCRIPTION BESCHREIBUNG	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



LENGTH SCHEDULE:

TE PART NO.	REV.	LENGTH L (mm)	TOL.	FORD PART NO.	RELEASE NO.	ALERT NO.
2141730-5	E	1110	+30	BU4T-18812-XB	-	-
2141730-7	C	830	+30	BU4T-18812-TC	-	-

NOTES

- 1 PACKAGING:
ASSEMBLIES PACKED IN TE STANDARD BOXES
ACC. TO TE SPECIFICATION 107-18087, 107-18064.
- 2 ELECTRICAL TEST ACC. TO SPECIFICATION 108-18857:
3.1.1 STANDARD CHECK ITEM: A (MAX. 1 OHM, TESTING WITH 5 V DC),
B (MIN. 1 KOHM, TESTING WITH 5 V DC), C, D.
3.1.2 SPECIAL CHECK ITEM: A (MIN. 100 MOHM, TESTING WITH 1000 V), D, N.
- 3 APPLICATION SPECIFICATION FOR FAKRA IV CONNECTOR SYSTEM IS 114-13157,
CRIMP HEIGHT OF CENTRE CONTACT AND FERRULE
ACCORDING APPLICATION SPECIFICATION.
- 4 LABEL TO BE APPLIED AFTER SUCCESSFUL ELECTRICAL TEST:
PRODUCTION DATE: YEAR, MONTH, DAY, SHIFT (YYYYMMDDS),
PRODUCTION LOCATION: 5 LETTER CODE OF THE PRODUCTION PLANT,
BARCODE - TYPE 128B: FORD PN,
2D CODE (DATAMATRIX): ACC. PRODUCTION PLANT REQUIREMENTS.
- 5 ALTERNATIVELY THE RTK 031 COAX CABLE PN 956339-3
CAN BE USED INSTEAD OF RTK 031 COAX CABLE PN 956339-2.

-	-	956339-2	COAX CABLE RTK 031 BIS 105 GRAD	11
1	1	1418972-1	CENTER CONTACT, JACK	10
1	1	2365471-2	SOCKET CONTACT, PLUG, 180 DEGREE, SMB	9
1	1	2365466-7	PIN CONTACT, JACK, 180 DEGREE, SMB	8
1	1	4-1768418-0	LABEL	7
1	1	2203238-1	PLUG SUBASSEMBLY, RTK031, FAKRA	6
1	1	1438893-2	1 POS. PLUG HOUSING, 180 DEGREE, CODE B	5
2	2	1488167-1	FERRULE, RTK031, 180 GRAD	4
1	1	1438888-1	1 POS. LOCK, 180 DEGREE, FAKR	3
1	1	1488170-2	JACK SUBASSEMBLY, RTK031, FAKRA II	2
1	1	1452581-2	1 WAY JACK COAX CONN FAKRA2, CODE B	1
QTY - 7	QTY - 5	PART NO.	DESCRIPTION	ITEM NO.
			WEIGHT OF ASSY NO. [g]	

DIESE ZEICHNUNG IST EIN KONTROLLIERTES DOKUMENT. BEMASSUNGEN UND TOLERANZEN GEMAESS GPS (ISO STANDARDS).		TOLERANCING EN ISO 8015 TOLERIERUNG EN ISO 8015	
THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER GPS (ISO STANDARDS).		DWN 14DEC2010 O. Snajder CHK 14DEC2010 P. Skrovaneck APVD 17DEC2010 R. Hort	
DIMENSIONS: MASSEINHEITEN: (MM)		TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLGEMEINTOLERANZEN	
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES/WINKEL ±	
MATERIAL		FINISH/OBERFLAECHE/FARBE	
-		-	
-		-	
CUSTOMER DRAWING		/KUNDENZEICHNUNG	
SCALE MASSSTAB 1:1		SHEET BLATT 4 OF 5 VON 5	
RESTRICTED TO NUR FUER		REV J	



NAME
FAKRA, RTK 031
CABLE ASSEMBLY


SIZE A3 CAGE CODE 00779 DRAWING NO. ZEICHNUNGS-NR. C=2141730

© 2019 TE Connectivity. All Rights Reserved.

THE DRAWING SHOWS THE 2-DIMENSIONAL REFERENCE COMPONENT CONDITION OF THE ASSEMBLY TO IDENTIFY AND SPECIFY THE NECESSARY DIMENSIONS ONLY. THE DELIVERED PARTS MAY DEVIATE FROM THE DRAWING REGARDING THE ORIENTATION AND POSITION OF EACH COMPONENT (e.g. SLACK CABLE), SO FAR THE FUNCTIONALITY IS NOT CONCERNED.

DIE ZEICHNUNG ZEIGT DEN 2-DIMENSIONALEN IDEALZUSTAND DES ZUSAMMENBAUTEILS BEZUEGLICH DER KOMPONENTEN ZUR IDENTIFIKATION UND SPEZIFIKATION DER NOTWENDIGEN DIMENSIONEN. HINSICHTLICH DER ORIENTIERUNG UND DER LAGE DER KOMPONENTEN (z.B. BIEGESCHLAFES KABEL) KOENNEN DIE GELIEFERTEN TEILE VON DER ZEICHNUNG ABWEICHEN, SOFERN DIE FUNKTIONALITAET NICHT BEEINTRAECHTIGT IST.


REVISIONS ÄNDERUNGEN					
P	LTR	DESCRIPTION BESCHREIBUNG	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



LENGTH SCHEDULE:

TE PART NO.	REV.	LENGTH L (mm)	TOL.	FORD PART NO.	RELEASE NO.	ALERT NO.
2141730-8	B	1320	+30	EU4T-18812-EA	-	-
2141730-9	B	855	+30	EU4T-18812-FA	-	-

TRANSIT LOOP



NOTES

- 1 PACKAGING:
ASSEMBLIES PACKED IN TE STANDARD BOXES
ACC. TO TE SPECIFICATION 107-18087, 107-18064.
- 2 ELECTRICAL TEST ACC. TO SPECIFICATION 108-18857:
3.1.1 STANDARD CHECK ITEM: A (MAX. 1 OHM, TESTING WITH 5 V DC),
B (MIN. 1 KOHM, TESTING WITH 5 V DC), C, D.
3.1.2 SPECIAL CHECK ITEM: A (MIN. 100 MOHM, TESTING WITH 1000 V), D, N.
- 3 APPLICATION SPECIFICATION FOR FAKRA IV CONNECTOR SYSTEM IS 114-13157,
CRIMP HEIGHT OF CENTRE CONTACT AND FERRULE
ACCORDING APPLICATION SPECIFICATION.
- PULL OUT FORCE OF CENTRE CONTACT MIN. 50 N.
- 4 LABEL TO BE APPLIED AFTER SUCCESSFUL ELECTRICAL TEST:
PRODUCTION DATE: YEAR, MONTH, DAY, SHIFT (YYYYMMDDS),
PRODUCTION LOCATION: 5 LETTER CODE OF THE PRODUCTION PLANT,
BARCODE - TYPE 128B: FORD PN,
2D CODE (DATAMATRIX): ACC. PRODUCTION PLANT REQUIREMENTS.
- 5 ALTERNATIVELY THE RTK 031 COAX CABLE PN 956339-3
CAN BE USED INSTEAD OF RTK 031 COAX CABLE PN 956339-2.

-	-	956339-2	COAX CABLE RTK 031 BIS 105 GRAD	9
2	2	2365471-2	SOCKET CONTACT, PLUG, 180 DEGREE, SMB	8
1	1	4-1768418-0	LABEL	7
1	1	1557159-1	CLIP FOR FAKRA HOUSING, FIXED	6
2	2	1488167-1	FERRULE, RTK031, 180 GRAD	5
2	2	2203238-1	PLUG SUBASSEMBLY, RTK031, FAKRA	4
1	1	1438894-2	1 POS. LOCK WITH BODY CLIP	3
1	1	1438888-1	1 POS. LOCK, 180 DEGREE, FAKR	2
2	2	2138710-1	1 POS.PLUG HOUSING,180 DEGREE, CODE A	1
QTY - 9	QTY - 8	PART NO.	DESCRIPTION	ITEM NO.
-	-	WEIGHT OF ASSY NO. [g]		

DIESE ZEICHNUNG IST EIN KONTROLLIERTES DOKUMENT. BEMASSUNGEN UND TOLERANZEN GEMAESS GPS (ISO STANDARDS).

THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER GPS (ISO STANDARDS).

DIMENSIONS: MASSEINHEITEN: (MM)	TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLGEMEINTOLERANZEN	DWN O. Snajder 14DEC2010	TOLERANCING EN ISO 8015 TOLERIERUNG EN ISO 8015
0 PLC ±	1 PLC ±	CHK P. Skrovaneck 14DEC2010	 TE Connectivity
2 PLC ±	3 PLC ±	APVD R. Hort 17DEC2010	
4 PLC ±	ANGLES/WINKEL ±	PRODUCT SPEC PRODUKTSPEZ.	NAME FAKRA, RTK 031 CABLE ASSEMBLY
MATERIAL	FINISH/OBERFLAECHE/FARBE	APPLICATION SPEC VERARBEITUNGSSPEZ.	SIZE A3
-	-	WEIGHT GEWICHT	CAGE CODE 00779
-	-	CUSTOMER DRAWING	DRAWING NO. ZEICHNUNGS-NR. G=2141730
		SCALE MASSSTAB 1:1	RESTRICTED TO NUR FUER
		SHEET BLATT 5 OF 5	REV J