



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
FT	0	P	LTR	DESCRIPTION	DATE	DWN	APVD
			B1	REVISED PER ECO-10-009052	29APR10	HMR	CR

MATERIAL:  
 HOUSING: PBT, UL94V-0, BLACK.  
 TERMINAL: BRASS, TIN PLATED.  
 SCREWS: 3M, STEEL, NICKEL PLATED.

ELECTRICAL:  
 CURRENT RATING: 15A, 300V.  
 WIRE RANGE: 16-22 AWG.

MECHANICAL:  
 RECOMMENDED TORQUE: 12 IN-LB  
 OPERATING TEMP.: -40°C TO +120°C



207.95	198.00	25	2-1776859-5
199.70	189.75	24	2-1776859-4
191.45	181.50	23	2-1776859-3
183.20	173.25	22	2-1776859-2
174.95	165.00	21	2-1776859-1
166.70	156.75	20	2-1776859-0
158.45	148.50	19	1-1776859-9
150.20	140.25	18	1-1776859-8
141.95	132.00	17	1-1776859-7
133.70	123.75	16	1-1776859-6
125.45	115.50	15	1-1776859-5
117.20	107.25	14	1-1776859-4
108.95	99.00	13	1-1776859-3
100.70	90.75	12	1-1776859-2
92.45	82.50	11	1-1776859-1
84.20	74.25	10	1-1776859-0
75.95	66.00	9	1776859-9
67.70	57.75	8	1776859-8
59.45	49.50	7	1776859-7
51.20	41.25	6	1776859-6
42.95	33.00	5	1776859-5
34.70	24.75	4	1776859-4
26.45	16.50	3	1776859-3
18.20	8.25	2	1776859-2
DIM B	DIM A	NO. OF POS.	PART NUMBER

1 TE LOGO LOCATED APPROXIMATE AREA SHOWN.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	S SCHLEGEL	23JUN2006	Tyco Electronics Corporation Harrisburg, PA 17105-3608		
DIMENSIONS: mm		CHK	S YODER	6/23/06	NAME		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	S YODER	6/23/06	.325 DUAL BARRIER STRIP		
0 PLC ± -		PRODUCT SPEC		SIZE			
1 PLC ± 0.5		APPLICATION SPEC		CAGE CODE		DRAWING NO	
2 PLC ± -		MATERIAL		A3		00779	
3 PLC ± -		FINISH		G=		1776859	
4 PLC ± -		MATERIAL		CUSTOMER DRAWING		RESTRICTED TO	
ANGLES ± 1°		MATERIAL		SCALE		SHEET	
FINISH		MATERIAL		2:1		1 OF 1	
MATERIAL		MATERIAL		REV		B1	