





THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT - BY - ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD		
B		REVISED PER ECO-12-018187	2NOV2012	CT	KH		



MATING FACE



- 1 FRONT & REAR INSULATORS: HIGH-TEMP THERMOPLASTIC OR THERMOSET EPOXY PER ASTM D5948.  
 CONTACT RETENTION CLIPS: STAINLESS STEEL PER AISI 302 OR COPPER ALLOY PER ASTM B194  
 REAR GROMMET & INTERFACIAL SEAL: FLUOROSILICONE ELASTOMER PER MIL-R-25988 B EXCEPT 4.6.6.1.
- 2 PART TO BE MARKED WITH TE IDENTIFICATION, TE PART NO.  
 AND DATE CODE: YEAR & WEEK (YY WW) IN APPROXIMATE AREA SHOWN.
- 3. THIS INSERT CONTAINS: 24 CAVITIES FOR SIZE 22 PIN CONTACTS  
 1 CAVITY FOR SIZE 8 QUADRAX PIN CONTACTS.
- 4. THIS PRODUCT IS SOLD BY TYCO ELECTRONICS UNDER A LICENSE FROM RADIALL SA.

THIS PRODUCT HAS NOT COMPLETED VALIDATION TESTING

ENVIRONMENTAL	GPRBE25QISB	1877568-1
REMARKS	DISCRIPTIVE PART NUMBER	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	8NOV07	TE Connectivity
		CHK	8NOV07	
		APVD	8NOV07	
		PRODUCT SPEC		
DIMENSIONS:				NAME
mm				INSERT ASSEMBLY, SOCKET, ENVIRONMENTAL, ARRANGEMENT 25Q1, KEY B, GPRB
TOLERANCES UNLESS OTHERWISE SPECIFIED:				SIZE
0 PLC	±			A200779
1 PLC	±			CAGE CODE
2 PLC	±0.05			C-1877568
3 PLC	±			DRAWING NO
4 PLC	±			RESTRICTED TO
ANGLES	±			
FINISH	±			
MATERIAL				SCALE
				4:1
				SHEET
				OF
				REV
				C