





LOC	DIST	REVISIONS					
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
		C		UPDATE P/N	03JUL2014	J.G	C.Z
		D		REVISED PER ECO-17-006848	10MAY2017	JM	SS
		E		REVISED PER ECO-19-001409	01FEB2019	AP	RP
		F		REVISED PER ECN-24-258247	28MAR2024	RZ	HL



- 1 HOUSING: THERMOPLASTIC, UL 94V-0, BLACK. CONTACT: COPPER ALLOY.
- 2 CONFORMS TO REQUIREMENTS OF TE PRODUCT SPEC 108-2413, BASED ON TELECORDIA GR-1217-CORE FOR SYSTEM QUALITY LEVEL III APPLICATIONS IN CONTROLLED ENVIRONMENTS (CENTRAL OFFICE).
- 3 CONSULT APPLICATION SPECIFICATION 114-13301.
- 4 PLATED THRU HOLE REQUIREMENTS:
 FINISHED HOLE = $\varnothing 0.344 \pm 0.046$ mm
 DRILLED HOLE BEFORE PLATING = $\varnothing 0.420 \sim 0.435$ mm
 COPPER THICKNESS = 0.042mm REF
- 5 PLATED THRU HOLE DIMENSIONS APPLY TO 1.00mm DEPTH FROM MOUNT SIDE OF BOARD.
- 6 HOLE POSITION TOLERANCE APPLIES WITHIN PATTERN FOR CONNECTOR PATTERN TO CONNECTOR PATTERN, A 0.12(M) POSITION TOLERANCE APPLIES.
- 7 CONNECTOR MARKED WITH PART NUMBER, DATE CODE, AND OPTIONAL MANUFACTURING LOCATION IDENTIFICATION CODE IN APPROXIMATE AREA SHOWN.
- 8 CONNECTOR MARKED WITH 2D BARCODE IN APPROXIMATE AREA SHOWN.




OBSELETE

SECTION J-J

ACTIVE	96	4.125	25.4	TIN	2180822-5		
ACTIVE	96	3.625	24.4	TIN	2180822-4		
ACTIVE	96	3.625	24.4	TIN-LEAD	2180822-2		
ACTIVE	96	4.125	25.4	TIN-LEAD	2180822-1		
PART STATUS	SIGNAL CONTACT QTY REF	Y	X	PRESS FIT TAIL PLATING	PART NO		
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. SHIRK 15JUN2011	TE Connectivity NAME: HEADER ASSEMBLY, 8 PAIR 6 COLUMN, 4.5mm, STRADA WHISPER				
DIMENSIONS: mm		CHK N. SWANGER 15JUN2011					
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD N. SWANGER 15JUN2011					
0 PLC	±	PRODUCT SPEC	2	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
1 PLC	±	APPLICATION SPEC	3	A2	00779	C-2180822	
2 PLC	±0.10			WEIGHT			
3 PLC	±			CUSTOMER DRAWING	SCALE 5:1	SHEET 1 OF 2	REV F
4 PLC	±						
ANGLES	±						
FINISH	±						
1	SEE TABLE						

LOC	DIST	REVISIONS					
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
		-		SEE SHEET 1			



TOP SURFACE OF DAUGHTERCARD

- = SIGNAL
- ⊗ = GROUND
- ⊙ = SI VIA

RECOMMENDED PCB LAYOUT BACKPLANE
 COMPONENT SIDE SHOWN
 SCALE 10:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. SHIRK 15JUN2011	 TE Connectivity	NAME		
DIMENSIONS: mm		CHK N. SWANGER 15JUN2011		HEADER ASSEMBLY, 8 PAIR 6 COLUMN, 4.5mm, STRADA WHISPER		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD N. SWANGER 15JUN2011		SIZE	CAGE CODE	DRAWING NO
0 PLC ±		PRODUCT SPEC		A2	00779	C-2180822
1 PLC ±		APPLICATION SPEC	WEIGHT	SCALE 5:1	SHEET 2 OF 2	
2 PLC ±0.10			CUSTOMER DRAWING	REV F		
3 PLC ±						
4 PLC ±						
ANGLES ±						
FINISH						