




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A1		ECO-20-012134	28NOV2020	RK	JO



- 1 .000003-.000005 GOLD OVER .0000027 PALLADIUM NICKEL IN CONTACT AREA, GOLD FLASH OVER ENTIRE RECEPTACLE, ALL OVER .000050 NICKEL.
- 2 .000003-.000005 GOLD OVER .0000027 PALLADIUM NICKEL IN CONTACT AREA, BRIGHT TIN-LEAD IN AREA K, ALL OVER .000050 NICKEL.
- 3 .000003-.000005 GOLD OVER .0000027 PALLADIUM NICKEL IN CONTACT AREA, MATTE TIN IN AREA K, ALL OVER .000050 NICKEL.
- 4 REELED FOR MINI APPLICATOR.
- 5 GOLD PLATING NOT REQUIRED - THIS AREA.
- 6 REELED FOR STANDARD APPLICATOR
- 7 POINT OF MEASUREMENT FOR PLATING THICKNESS (INSIDE BEAMS).
- 8 SHEARED EDGES ARE PERMITTED TO BE UNPLATED.
- 9 CUT OUTS ON BOX AT MANUFACTURER'S OPTION.
- 10 PRELIMINARY PART - NOT RELEASED FOR PRODUCTION.
- 11 OBSOLETE



WIRE SIZE #20-#24

DESCRIPTION	FINISH	PART NUMBER
LOOSE PIECE	3	1977968-7
REELED	3	1977968-6
LOOSE PIECE	2	1977968-5
REELED	2	1977968-4
LOOSE PIECE	1	1977968-3
REELED	1	1977968-2

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 07MAY2014 NAGALAKSHMI K	TE TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK 07MAY2014 OLSON, JOSEPH		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 07MAY2014 OLSON, JOSEPH	NAME	
0 PLC ± -	1 PLC ± -	PRODUCT SPEC	CONTACT, MOD IV	
2 PLC ± 0.13[.005]	3 PLC ± -	APPLICATION SPEC	CRIMP SNAP-IN RECEPTACLE	
4 PLC ± -	ANGLES ± -		PALLADIUM NICKEL PLATED	
MATERIAL CU-SN-P, ALY 521	FINISH SEE TABLE	WEIGHT 0.000000	SIZE A2	CAGE CODE 00779
		CUSTOMER DRAWING	DRAWING NO C=1977968	RESTRICTED TO -
		SCALE 10:1	SHEET 1 of 1	REV A1