







LOC		DIST		REVISIONS					
-	-	-	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
						-	-	-	-




- 1 HOUSING: THERMOPLASTIC, COLOR BLACK, FLAMMABILITY RATING UL 94 V-0.
- 2 THIS ASSEMBLY TO MATE WITH TEC PART NUMBER 2212311-1.
3. RECOMMENDED SHOULDER SCREW:
2212056, FLOAT MOUNT
2212055, FIXED MOUNT
- 4 RECOMMENDED PANEL CUTOUT FOR FRONT PANEL MOUNT APPLICATION.
RECOMMENDED PANEL THICKNESS 1.5 TO 1.78.
- 5 DATE CODE AND PART NUMBER IN APPROXIMATE AREA SHOWN.



FULLY MATED ASSEMBLIES 2

CONNECTOR, PIN, FORGE 0x#0,6x#4,0x#8,0x#12,0x#22						2212309-1			
DESCRIPTION						PART NO.			
THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONS: mm TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±N/A 1 PLC ±N/A 2 PLC ±0.25 3 PLC ±0.13 4 PLC ±N/A ANGLES ±N/A FINISH -						DWN R. TREA 18FEB2015 CHK E. WICKES 18FEB2015 APVD D. ORRIS 18FEB2015 NAME PRODUCT SPEC 108-2323 APPLICATION SPEC 114-13299 WEIGHT - Customer Drawing			
THIS PRINT IS PRELIMINARY UNQUALIFIED PRODUCT CONTACT PRODUCT ENGINEERING BEFORE USING THIS PRINT						TE Connectivity CONNECTOR, PIN, FORGE 0x#0,6x#4,0x#8,0x#12,0x#22 CONFIGURATION SIZE CAGE CODE DRAWING NO A100779C=2212309 RESTRICTED TO -			
						SCALE 1:1 SHEET 1 OF 2 REV 1			



RECOMMENDED PANEL CUTOUT 
SCALE 2:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN 181BF2015		 TE Connectivity	
		CHG 181BF2015			
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME CONNECTOR, PIN, FORGE 0x0, 6x#4, 0x8#8, 0x#12, 0x#22 CONFIGURATION	
mm		mm			
		Ø PLC ±0.04 PLC ±0.04 PLC ±0.05 PLC ±0.13 PLC ±0.13 ANGLES ±3°			
		PRODUCT SPEC 108-2323 APPLICATION SPEC 114-13299			
MATERIAL		WEIGHT		SIZE CASE CODE DRAWING NO A100779C2212309	
FINISH		Customer Drawing		RESTRICTED TO SCALE 1:1 SHEET 2 OF 2 REV 1	