




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	0				
			15DEC2008	SS	CR




THIS PRINT IS
PRELIMINARY
 THE INFORMATION CONTAINED IN THIS DOCUMENT IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS
 DO NOT REPRODUCE OR DISTRIBUTE
 DESIGN IS SUBJECT TO CHANGE WITHOUT NOTICE

1. MATERIALS AND FINISH
 HOUSING: PA 6-6, UL 94-V0, COLOR: GRAY RAL 7035.
 CLAMP: BRASS, NICKEL PLATED.
 TERMINAL: BRASS, TIN PLATED.
 CLAMPING SCREW: M3, BRASS, NICKEL PLATED.
2. SUITABLE FOR 1,6-2,4mm PC BOARD THICKNESS.
3. END-TO-END STACKABLE W/INTERLOCK WITHOUT LOSS OF CENTERLINE SPACING.
4. WIRE SIZE RANGE
 12 - 30 AWG
5. RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC. FILE N° E60677.
6. IMQ CERTIFICATE WITH SURVEILLANCE IN CONFORMITY WITH IEC 998-1/998-2-1.
7. NOT CUMULATIVE TOLERANCE.



102.5	100	20	2-1986505-0
82.5	80	16	1-1986505-6
62.5	60	12	1-1986505-2
52.5	50	10	1-1986505-0
42.5	40	8	1986505-8
17.5	15	3	1986505-3
12.5	10	2	1986505-2
B	A	NO OF POSN	PART NUMBER



THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DWN	S SCHLEGEL	15DEC2008	Tyco Electronics Harrisburg, PA 17105-3608	
mm		CHK	C RICHARD	15DEC2008		
	0 PLC ±.3	APVD	C RICHARD	15DEC2008		
	1 PLC ±.25	PRODUCT SPEC		108-20166		
	2 PLC ±.25	APPLICATION SPEC		114-20079	NAME	TERMINAL BLOCK, PCB MOUNT 1ST AND 2ND LEVEL STACKING W/INTERLOCK, 5mm PITCH
	3 PLC ±.	WEIGHT		-	SIZE	A3
	4 PLC ±.				CAGE CODE	00779
	ANGLES ±.2				DRAWING NO	C-1986505
MATERIAL	FINISH				RESTRICTED TO	-
					CUSTOMER DRAWING	

SCALE 2:1 SHEET 1 OF 1 REV 1