

4


3

2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT - by - ALL RIGHTS RESERVED.




LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	ECR-14-000783	17JAN2014	E.C	K.Z



- PRODUCT SPECIFICATION:
1. Rated Current:3.0AMP.
  2. Contact Resistance:20mΩ Max.
  3. Withstand Voltage:1000V AC/DC
  4. Insulation Resistance:1000MΩ Min.
  5. Operation Temperature:-40°C to +105°C
  6. Peak Temperature: 260°C

MATERIAL:  
 CONTACT: Brass H65  
 HOUSING: PA9T+GLASS FIBER UL94V-0 BK

FINISH:  
 ① 30u" Au Over 30~80u" Ni on Mating area,  
 ② 100u" Min. Sn Over 30~80u" Ni on Solder area



Recommended P.C.B Layout (Top View)

2.29	6.33	25.16	2232366-5
2.79	5.59	22.86	2232366-4
2.54	6.97	19.19	2232366-3
2.41	6.08	15.13	2232366-2
2.79	5.44	12.85	2232366-1
C	B	A	PN

PART FAMILY TABLE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN ETHAN CHENG 15-NOV-13		TE Connectivity
CHK KOBBOY ZHAO 16-NOV-13		
APVD XU XIANG 17-NOV-13	NAME	
PRODUCT SPEC	AMPMODU, 2.54 PITCH, 10 POSITION, PIN HEADER, THROUGH HOLE	
APPLICATION SPEC	SIZE	RESTRICTED TO
MATERIAL	CAGE CODE	DRAWING NO
WEIGHT	A2 00779	2232366
FINISH	SCALE	SHEET
SEE NOTES	1:1	1 of 1
SEE NOTES	CUSTOMER DRAWING	REV B1