







LOC		DIST		REVISIONS			
P	LTN	DESCRIPTION	DATE	DWN	APVD		
A		REVISED PER ECR-13-003618	14MAR2013	KH	TM		
A1		REVISED PER ECR-21-119230	08NOV2021	SS	VS		



1. PARTS COMPLY TO AMP SOLDERABILITY SPECIFICATION 109-11-3.
2. PARTS MOLDED WITHOUT DRAIN HOLES.
3. CIRCUIT IDENTIFICATION CHARACTERS ARE ADJACENT TO THE INDICATED CAVITIES, BUT LOCATION AND ORIENTATION MAY DIFFER FROM PRINT.
4. DIMENSIONS IN BRACKETS ARE IN INCHES.
5. PRE PRODUCTION - FAAR REQUIRED
6. DIMENSIONS SHOWN REPRESENT PRODUCT IN DRY CONDITION. ADDITIONAL 2% GROWTH DUE TO END USE LOCATION MOISTURE ABSORPTION MAY OCCUR AND SHOULD BE ACCOUNTED FOR.



3 DIMENSIONAL MODEL  
SCALE 4:1



RECOMMENDED MOUNTING HOLE PATTERN FOR 3.17 [.125] THICK P.C. BOARD

PHOSPOR BRONZE, PRE-TIN		NYLON, UL94-V2, NATURAL		2029451-1/3	
PIN CONTACT MATERIAL AND FINISH		HOUSING MATERIAL AND COLOR		PART NUMBER	
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RIRAN, HOLA 01JAN2013		TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK MICHELUTTI, THOMAS 01JAN2013		NAME SOCKET HEADER ASSEMBLY, 6 CIRCUIT, UNIVERSAL MATE-N-LOK™	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD MICHELUTTI, THOMAS 01JAN2013		SIZE CAGE CODE DRAWING NO RESTRICTED TO	
0 PLC ±		PRODUCT SPEC		A100779C=2029451	
1 PLC ±		APPLICATION SPEC		SHEET 1 OF 1 REV A1	
2 PLC ±0.25(.010)		WEIGHT		SCALE 4:1	
3 PLC ±		Customer Drawing		SHEET 1 OF 1 REV A1	
4 PLC ±					
ANGLES ±40°30'					
FINISH SEE TABLE					