

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

-,-



COPYRIGHT 2011

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD







C

REVISED AS PER ECN-22-176158

02AUG'22

HS

SZ



NOTES:

- MATERIAL:
HOUSING: PA9T WITH 33% GF, UL94 V-0, BLACK COLOR.
CONTACTS: PHOSPHOR BRONZE.
SHELL: PHOSPHOR BRONZE.
MYLAR: POLYAMIDE FILM.
- FINISH:
CONTACTS: GOLD FLASH OVER
0.762μm [30μ"] MIN. PALLADIUM-NICKEL OR ALTERNATIVE
0.762μm [30μ"] MIN. GOLD PLATED ON CONTACT AREA,
2.54μm [100μ"] MIN. MATTE-TIN ON SOLDER TAIL,
WITH ENTIRE CONTACT UNDERPLATED 1.27μm [50μ"] MIN. NICKEL.
SHELL: 2.03μm [80μ"] MIN. NICKEL PLATED.
- NO DATECODE ON PRODUCT SURFACE.
- REFLOW SOLDER CAPABLE TO 260°C PER TEC 109-201, METHOD B, CONDITION B.

2041492-1

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 16JAN2012

A. WU

CHK 16JAN2012

S. CHIEN

APVD 16JAN2012

W. KODAMA

PRODUCT SPEC

108-57062

APPLICATION SPEC

WEIGHT

-

CUSTOMER DRAWING



TE Connectivity

NAME

MINI USB, R/A, SMT, B TYPE

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-2041492

SCALE

-

SHEET

1 OF 2

REV

C

