


Τ	REVISIONS							
r	Р	LTR		DESCRIPTION	Di	ATE	DWN	APVD
Γ		Α	OFFICIAL VERS	SION RELEASE	18DE	C2015	F.Y	X.X
	A1 PER ECR-16-006247			-006247	16JU	N2016	F.Y	X.X

С

В






NO	TE:
----	-----

- 1. Material: See Table
- 2. Operation temperature: -40°C to +105°C
- 3. Wire strip length: 8mm -10mm
- 4. Suitable wire size: 28 14 AWG
- 5. Requirement for environmental substance must be compliance with ROHS and REACH.
- 6. Recommanded support rail requirements refer to 114 application specification.

4	GROUND TERMINAL	COPPER ALLOY	1	TIN PLATED
3	SPRING CLAMP	STAINLESS STEEL	2	
2	TERMINAL	COPPER	1	TIN PLATED
1	HOUSING	THERMOPLASTIC	1	
ITEM	COMPONENTS	MATERIAL	Q'TY	PLATING

2



THIS DRAWING IS A CO	ONTROLLED DOCUMENT.	DWN 16JUN2016 FENCER YU CHK 16JUN2016	TE Connectivity	1
DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD 16JUN2016 XIANG XU	1.5mm^2 WIRE 1 IN 1 OUT SPRING CLAMP	1
0 PLC ± 0.50 1 PLC ± 0.40 2 PLC ± 0.30 3 PLC ± -		108-137142  APPLICATION SPEC	TYPE TERMINAL BLOCK WITH GROUND FUNCTION	
1	4 PLC ± - ANGLES ± 3°	114-137138	SIZE CAGE CODE DRAWING NO RESTRICTED TO	ণ
MATERIAL	FINISH	<b>weight</b> 8.0 g	A3 00779 C=2271574 -	
1	_	CUSTOMER DRAWING	SCALE 1:1 SHEET 1 OF 1 REV A1	

В