


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
COPYRIGHT - By - ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
A		OFFICIAL VERSION RELEASE	18DEC2015	F.Y	X.X
A1		PER ECR-16-006247	16JUN2016	F.Y	X.X



NOTE:

1. Material: See Table
2. Rated current & voltage : 10Amp ,250V(follow LED)
3. Rated surge voltage: 4KV
4. Operation temperature : -40°C to +105°C
5. Wire strip length: 8mm -10mm
6. Suitable wire size : 28 - 10 AWG
7. Fuse:G/5x20
8. Requirement for environmental substance must be compliance with ROHS and REACH.
9. Recommended support rail requirements refer to 114 application specification.

ITEM	COMPONENTS	MATERIAL	Q'TY	PLATING
7	COVER	THERMOPLASTIC	1	
6	SPRING CLAMP	STAINLESS STEEL	2	
5	SPRING	COPPER ALLOY	2	
4	LED MODULE	/	1	
3	HOUSING 2	THERMOPLASTIC	1	
2	TERMINAL	COPPER	4	TIN PLATED
1	HOUSING 1	THERMOPLASTIC	1	

DTS4 FULED 250	2271585-1	BLACK
TE SERIES No.	PART NUMBER	COLOR

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN FENCER YU 16JUN2016	TE Connectivity	
CHK KOBBY ZHAO 16JUN2016		
APVD XIANG XU 16JUN2016	NAME 4mm ² WIRE 1 IN 1 OUT SPRING CLAMP TERMINAL BLOCK ,FUSE TYPE WITH LED	
PRODUCT SPEC 108-137138	SIZE A3	
APPLICATION SPEC 114-137138	CAGE CODE 00779	
MATERIAL -	WEIGHT 14.55g	
FINISH -	DRAWING NO C=2271585	
CUSTOMER DRAWING		RESTRICTED TO -
SCALE 1:1		SHEET 1 OF 1
REV A1		