

4

3

2

1

THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.




© COPYRIGHT - By -

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	OFFICIAL VERSION RELEASE	18DEC2015	F.Y	X.X
	A1	PER ECR-16-006247	16JUN2016	F.Y	X.X



ITEM	COMPONENTS	MATERIAL	Q'TY	PLATING
4	GROUND TERMINAL	COPPER ALLOY	1	TIN PLATED
3	SPRING CLAMP	STAINLESS STEEL	2	
2	TERMINAL	COPPER	1	TIN PLATED
1	HOUSING	THERMOPLASTIC	1	



DTS 4-G	2271586-1	GREEN
TE SERIES No.	PART NUMBER	COLOR

NOTE:

1. Material: See Table
2. Operation temperature : -40°C to +105°C
3. Wire strip length: 8mm -10mm
4. Suitable wire size : 28 - 10 AWG
5. Requirement for environmental substance must be compliance with ROHS and REACH.
6. Recommended support rail requirements refer to 114 application specification.

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD		NAME		RESTRICTED TO	
mm				16JUN2016		4mm~2 WIRE 1 IN 1 OUT SPRING CLAMP TYPE TERMINAL BLOCK WITH GROUND FUNCTION		-	
		0 PLC	± 0.50	CHK		TE TE Connectivity 4mm~2 WIRE 1 IN 1 OUT SPRING CLAMP TYPE TERMINAL BLOCK WITH GROUND FUNCTION		-	
		1 PLC	± 0.40	FENCER YU					
		2 PLC	± 0.30	16JUN2016		PRODUCT SPEC 108-137142		-	
		3 PLC	± -	KOBBY ZHAO					
-		4 PLC	± -	16JUN2016		APPLICATION SPEC 114-137138		-	
		ANGLES	± 3°	XIANXU XU					
MATERIAL		FINISH		WEIGHT		SIZE		CAGE CODE	
-		-		11.67 g		A3		00779	
CUSTOMER DRAWING				SCALE		DRAWING NO		REV	
				1:1		C=2271586		1 OF 1	
								A1	