




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	OFFICIAL VERSION RELEASE	18DEC2015	F.Y	X.X
	A1	PER ECR-16-000663	15JAN2016	F.Y	X.X
	A2	PER ECR-16-006247	16JUN2016	F.Y	X.X



ITEM	COMPONENTS	MATERIAL	Q'TY	PLATING
4	GROUND TERMINAL	COPPER ALLOY	3	TIN PLATED
3	SPRING CLAMP	STAINLESS STEEL	2	
2	TERMINAL	COPPER	1	TIN PLATED
1	HOUSING	THERMOPLASTIC	1	



NOTE:

1. Material: See Table
2. Operation temperature : -40°C to +105°C
3. Wire strip length: 16mm -18mm
4. Suitable wire size : 24 - 6 AWG
5. Requirement for environmental substance must be compliance with ROHS and REACH.
6. Recommended support rail requirements refer to 114 application specification.

DTS10-G	2271590-1	GREEN
TE SERIES No.	PART NUMBER	COLOR

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN FENCER YU 16JUN2016	TE Connectivity		
		CHK KOBBY ZHAO 16JUN2016			
DIMENSIONS: mm 		APVD XIANG XU 16JUN2016	NAME		
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 0.50 1 PLC ± 0.40 2 PLC ± 0.30 3 PLC ± - 4 PLC ± - ANGLES ± 3°		PRODUCT SPEC 108-137142	10mm ² WIRE 1 IN 1 OUT SPRING CLAMP TYPE TERMINAL BLOCK WITH GROUND FUNCTION		
MATERIAL - FINISH -		APPLICATION SPEC 114-137138	SIZE A3	CAGE CODE 00779	DRAWING NO C=2271590
		WEIGHT 32.92 g	RESTRICTED TO -		
CUSTOMER DRAWING			SCALE 1:1	SHEET 1 OF 1	REV A2