


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	ECR-22-157330	22SEP2023	MAR	B.P

NOTES:

Tolerances cable lengths:
 0m to 0.5m +30mm
 0.5m to 1.0m +50mm
 1.0m to 3.0m +100mm
 < 3.0m +1.5%



PVC Cable	
No./diameter of wires	5 x 0.34 mm ²
Wire isolation	PVC (br, wh, bl, bk, gnye)
C-track properties	
Jacket	PVC (UL/CSA)
Outer diameter	approx. 5.2 mm
Bend radius (moving)	10 x outer diameter
Temperature range (fixed)	-30...+80 °C
Temperature range (mobile)	-5...+80 °C

TECHNICAL DATA	
Operating voltage	max. 125 V AC/DC
Operating current per contact	max. 4 A
Locking of ports	Screw thread M12 x 1 mm (recommended torque 0.6 Nm) self-securing
Protection	IP65 and IP67 when plugged and screwed down (EN 60529)

PUR CABLE	
No./diameter of wires	5 x 0.34 mm ²
Wire isolation	PP (br, wh, bl, bk, gnye)
C-track properties	yes
Jacket	PUR (UL/CSA)
Outer diameter	approx. 5.0 mm
Bend radius (moving)	10 x outer diameter
Temperature range (fixed)	-50...+80 °C
Temperature range (mobile)	-25...+80 °C

LENGTH "L"	MATERIAL	JACKET COLOR	TE PN	DESCRIPTION	ITEM
OBSOLETE 5 pos	PVC	Black	1-2273118-5	5x22AWG PVC 2.0m	10
			1-2273118-4	5x22AWG PVC 1.5m	9
			1-2273118-3	5x22AWG PVC 1.0m	8
			1-2273118-2	5x22AWG PVC 0.6m	7
OBSOLETE 5 pos	PUR	Black	1-2273118-1	5x22AWG PVC 0.3m	6
			2273118-5	5x22AWG PUR 2.0m	5
			-2273118-4	5x22AWG PUR 1.5m	4
			-2273118-3	5x22AWG PUR 1.0m	3
			2273118-2	5x22AWG PUR 0.6m	2
2273118-1	5x22AWG PUR 0.3m	1			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN YATHISH.C 29NOV2013	TE Connectivity		
DIMENSIONS: mm		CHK B.VELDHOVEN 29NOV2013			
		APVD A.VAN ZANDVOORT 29NOV2013	NAME M12 STRGT PLUG TO M12 ANGLED SOCKET AA		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	-		
0 PLC ± -		APPLICATION SPEC	-		
1 PLC ± -		WEIGHT	-		
2 PLC ± -		SIZE	A3	CAGE CODE	00779
3 PLC ± -		DRAWING NO	C-2273118		RESTRICTED TO
4 PLC ± -		CUSTOMER DRAWING			
ANGLES ± -		SCALE	NTS		SHEET
FINISH		1 OF 1		REV	A1