




REVISIONS				
P	LTN	DESCRIPTION	DATE	OWN APVD
C2		REVISED PER ECO-15-004915	09APR2015	AP DD
C3		REVISED PER ECN-24-252171	23FEB2024	AP RS





- ⚠ MATERIAL:
HOUSING: LCP, GLASS FILLED, UL94V-0.
TERMINALS: HIGH PERFORMANCE COPPER ALLOY.
- ⚠ FINISH:
30μ" SELECTIVE GOLD IN CONTACT AREA. SELECTIVE TIN ON PCB TAILS, NICKEL OVERALL.
- 3. CONNECTORS SUPPLIED WITH MOUNTING SCREWS.



SCALE 4:1

REFER TO WWW.TE.COM FOR PRODUCT AVAILABILITY



KEY POSITION CHART	
	NONE
	A
	B
	C
	D
	E
	F
	G
	H

180X Ø0.39±0.05 PLATED THRU HOLE
 180X Ø0.48±0.013 DRILL HOLE
 Ø0.10

OFFSET BETWEEN BOARD AND BACKPLANE HOLE COLUMNS

RECOMMENDED PCB LAYOUT
 MIN BOARD THICKNESS 1.0

KEY POSITION	FINISH	PART NUMBER
H	⚠	8-2110111-1
G	⚠	7-2110111-1
F	⚠	6-2110111-1
E	⚠	5-2110111-1
D	⚠	4-2110111-1
C	⚠	3-2110111-1
B	⚠	2-2110111-1
A	⚠	1-2110111-1
NONE	⚠	2110111-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	OWN: Z. MILLER 17SEP2010	CHK: D. DIXON 17SEP2010	APVD: D. DIXON 17SEP2010
mm	0 PLC ±0.2 1 PLC ±0.2 2 PLC ±0.10 3 PLC ±0.10 4 PLC ±0.10 ANGLES ±0.5	NAME: IMPACT, STD, R/A, 5 PAIR, 12 COLUMN, DAUGHTERCARD, RIGHT GUIDED SIGNAL MODULE, 0.39 EYELET	SIZE: A1	CAGE CODE: 00779
MATERIAL:	SEE TABLE	WEIGHT:	SCALE: 6:1	SHEET: 1 OF 1
CUSTOMER DRAWING		REV: C3	RESTRICTED TO	