




REVISIONS				
P.	LTN.	DESCRIPTION	DATE	APVD.
B		REVISED PER ECO-15-004915	14APR2015	AP DD





MATERIAL:
 HOUSING: LCP, GLASS FILLED, UL94V-0.
 TERMINALS: HIGH PERFORMANCE COPPER ALLOY.
 FINISH:
 30µ" SELECTIVE GOLD IN CONTACT AREA. SELECTIVE TIN ON PCB TAILS, NICKEL OVERALL.
 3. CONNECTORS SUPPLIED WITH MOUNTING SCREWS.



SCALE 4:1

REFER TO WWW.TE.COM FOR PRODUCT AVAILABILITY



KEY POSITION CHART	
	NONE

300X Ø0.39±0.05 PLATED THRU HOLE
 300X Ø0.48±0.013 DRILL HOLE
 Ø0.10

RECOMMENDED PCB LAYOUT
MIN BOARD THICKNESS 1.0

KEY POSITION	FINISH	PART NUMBER
H	△	8-2132954-1
G	△	7-2132954-1
F	△	6-2132954-1
E	△	5-2132954-1
D	△	4-2132954-1
C	△	3-2132954-1
B	△	2-2132954-1
A	△	1-2132954-1
NONE	△	2132954-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	OWN: B. CARBO 07JAN2011	TE Connectivity
mm	0 PLC ±	CHK: D. DIXON 07JAN2011	NAME: IMPACT, 5 PAIR, DAUGHTERCARD 20 COLUMN, RIGHT GUIDED, SIGNAL MODULE, 0.39 EYELET
	1 PLC ±0.2	APVD: D. DIXON 07JAN2011	
	2 PLC ±0.13	PRODUCT SPEC	SIZE: CAGE CODE DRAWING NO
	3 PLC ±	APPLICATION SPEC	RESTRICTED TO
	4 PLC ±	WEIGHT	A100779C=2132954
	ANGLES ±	Customer Drawing	SCALE 5:1 SHEET 1 OF 1 REV B