




SUGGESTED MATING TAB




Necessary space for housing to be inserted up to this line



TYPE A (When using tab shoulder for butting)



Butting surface of housing



TYPE B (When using resin, etc. for butting)



Shapping of the tab's hole must not exceed 0.08mm

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A9	ECR-24-204693	06MAY2024	DK	RE

NOTE:

- HOUSING MATERIAL, NYLON 6/66, GLASS-FIBRE. UL94V-0.
 - GWT 750°C VERSION ACCORDING TO ICE 60335-1.
 - CONTACT MATERIAL, TIN PLATED BRASS.
- △ NEW PART NUMBER WITH DIFFERENT PACKAGING QTY. AND SMALLER REELING SIZE (24in).



OBSOLETE	4.5 REF.	4.6	3.2 REF.	3.0	2.29-3.30	20-16	3-2299286-2
	3.4 REF.	4.1	2.1 REF.	2.3	1.52-2.79	24-20	3-2299286-1
	4.5 REF.	4.6	3.2 REF.	3.0	2.29-3.30	20-16	3-2299286-2
	3.4 REF.	4.1	2.1 REF.	2.3	1.52-2.79	24-20	2299286-1
	DIM D	DIM C	DIM B	DIM A	INSULATION (MM)	WIRE SIZE (AWG)	P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN: LEI PAN 08FEB2017
 CHK: TIM DING 08FEB2017
 APVD: TIM DING 08FEB2017

STE TE Connectivity

NAME: POD-LOK 187 STR. ASSY.

PRODUCT SPEC: 108-106262
 APPLICATION SPEC: 114-106262

MATERIAL: -
 FINISH: -

WEIGHT: -

SCALE: 2:1 SHEET 1 OF 1 REV A9