



REVISIONS				
P.	LTN.	DESCRIPTION	DATE	APVD.
1		INITIAL RELEASE	21MAY2018	BM KS



1. SEE SHEET 2 FOR WIRING SCHEMATIC.
2. ALL MATERIALS, COMPONENTS AND PROCESSES SHALL COMPLY WITH TEC-138-702. (CONTAIN NO BANNED OR RESTRICTED SUBSTANCES).
3. NO REACH SvHC SHALL BE CONTAINED ABOVE THE THRESHOLD AS DEFINED IN REACH SvHC COMPLIANCE DEFINITION IN ANNEX A OF TEC-138-702.
4. CABLE ASSEMBLY TO BE 100% TESTED FOR OPENS, SHORTS, PROPER EEPROM PROGRAM, AND SIGNAL INTEGRITY.

△ LABEL INFORMATION: -1 SHOWN.



3M 26AWG	3000±13	2336065-3
2.5M 26AWG	2500±13	2336065-2
2M 26AWG	2000±13	2336065-1
CONFIGURATION	"L"	PART NO

THIS PRODUCT HAS NOT COMPLETED VALIDATION AND QUALIFICATION TESTING

PRELIMINARY NOT RELEASED FOR PRODUCTION

THIS DRAWING IS A CONTROLLED DOCUMENT.



DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	OWN: B. MATTHEWS 02MAY2018	
mm	0 PLC ±	CHK: K. STAUFFER 02MAY2018	
	1 PLC ±	APVD: K. STAUFFER 02MAY2018	
	2 PLC ±	PRODUCT SPEC	
	3 PLC ±	APPLICATION SPEC	NAME: CABLE ASSEMBLY, OSFP, 26AWG
	4 PLC ±	WEIGHT	SIZE: CAGE CODE DRAWING NO: A100779
	ANGLES	CUSTOMER DRAWING	RESTRICTED TO: ©=2336065
MATERIAL:	FINISH:	SCALE: 5:1	SHEET 1 OF 2
			REV 1

REVISIONS				
P.	LTN	DESCRIPTION	DATE	APVD
-	-	SEE SHEET 1	-	-

P1			P2	
GND	1		31	GND
TX2+	2	↔	32	RX2+
TX2-	3	↔	33	RX2-
GND	4		34	GND
TX4+	5	↔	35	RX4+
TX4-	6	↔	36	RX4-
GND	7		37	GND
TX6+	8	↔	38	RX6+
TX6-	9	↔	39	RX6-
GND	10		40	GND
TX8+	11	↔	41	RX8+
TX8-	12	↔	42	RX8-
GND	13		43	GND
SCL	14		44	INT_L/RESET_L
VCC	15		45	VCC
VCC	16		46	VCC
PRSNT_L	17		47	SDA
GND	18		48	GND
RX7-	19	↔	49	TX7-
RX7+	20	↔	50	TX7+
GND	21		51	GND
RX5-	22	↔	52	TX5-
RX5+	23	↔	53	TX5+
GND	24		54	GND
RX3-	25	↔	55	TX3-
RX3+	26	↔	56	TX3+
GND	27		57	GND
RX1-	28	↔	58	TX1-
RX1+	29	↔	59	TX1+
GND	30		60	GND

P1			P2	
GND	31		1	GND
RX2+	32	↔	2	TX2+
RX2-	33	↔	3	TX2-
GND	34		4	GND
RX4+	35	↔	5	TX4+
RX4-	36	↔	6	TX4-
GND	37		7	GND
RX6+	38	↔	8	TX6+
RX6-	39	↔	9	TX6-
GND	40		10	GND
RX8+	41	↔	11	TX8+
RX8-	42	↔	12	TX8-
GND	43		13	GND
INT_L/RESET_L	44		14	SCL
VCC	45		15	VCC
VCC	46		16	VCC
SDA	47		17	PRSNT_L
GND	48		18	GND
TX7-	49	↔	19	RX7-
TX7+	50	↔	20	RX7+
GND	51		21	GND
TX5-	52	↔	22	RX5-
TX5+	53	↔	23	RX5+
GND	54		24	GND
TX3-	55	↔	25	RX3-
TX3+	56	↔	26	RX3+
GND	57		27	GND
TX1-	58	↔	28	RX1-
TX1+	59	↔	29	RX1+
GND	60		30	GND

WIRING PATTERN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: B. MATTHEWS 02MAY2018 CHK: K. STAUFFER 02MAY2018 APVD: K. STAUFFER 02MAY2018	 TE Connectivity	
DIMENSIONS: mm 	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±	PRODUCT SPEC APPLICATION SPEC WEIGHT	NAME: CABLE ASSEMBLY, OSFP, 26AWG SIZE: A1 CAGE CODE: 00779 DRAWING NO: 2336065	
MATERIAL: -		FINISH: -	CUSTOMER DRAWING SCALE: 5:1 SHEET: 2 OF 2 REV: 1	