

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

LOC

DIST

REVISIONS

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

GP

00

P

LTR

DESCRIPTION

DATE

DWN

APVD

B

INITIAL DRAWING

26AUG2015

DM

DM

NOTES:


1 EACH ITEM AND ASSEMBLY MUST COMPLY WITH EUROPEAN REDUCTION OF HAZARDOUS SUBSTANCES (RoHS) REGULATION. UNDER DIRECTIVE 2011/65/EU AND HARMONIZED STANDARD EN 50581:2012.

2 DO NOT SOLDER CONTACT, CRIMP ONLY

3 IDENTIFY POSITION PE, LOADING POSITIONER PE TO SOCKET PE

4 PE CONTACT CIRCUIT IDENTIFIED BY EXTENDED LENGTH POLARIZED "KEY"

5 ELECTRICAL TEST: 100% OPEN SHORT&MISS WIRE TEST CONTACT RESISTANCE: 2 OHM MAX



2829460-1

TE P/N

WIRING SCHEME	
CONNECTOR HOUSING (ITEM 1 and 7)	WIRE
PN/⊥	GREEN/YELLOW
N	BLUE
L	BROWN

3	PC	Socket Contacts, 2.5mm	8
1	PC	Socket Housing Assembly	7
AR	M	Cable, H07RN-F, 14/3 Black, 10.9-14.0mm OD (Mueller 4101403)	6
2	PC	Cable Ring Nut 11-14mm OD	5
2	PC	Cable Clamp/Seal Assembly 11-14mm OD	4
2	PC	Contact/Positioner Assembly	3
3	PC	Pin Contacts 2.5mm	2
1	PC	Pin Housing Assembly	1
QTY	UoM	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 25MAY2015

T.BURZYŃSKI

CHK 25MAY2015

A.V.ZANDVOORT

APVD 25MAY2015

A.V.ZANDVOORT

NAME


SEALED 3 POS PIN TO SEALED 3 POS SOCKET - STD HARMONIZED



TE Connectivity

DIMENSIONS:

mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± 0,5
1 PLC	± 0,5
2 PLC	± 0,5
3 PLC	± -
4 PLC	± -
ANGLES	± 2°

MATERIAL

FINISH

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=2829460

SCALE NTS

SHEET 1 OF 1

REV B

CUSTOMER DRAWING