

4

3

2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20  
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

NOTES:

1. MATERIALS:  
 HOUSING: GLASS-FILLED THERMOPLASTIC, UL 94V-0 RATED DIMMING CONTACTS (2 OR 4) AND LINE VOLTAGE CONTACTS (3): COPPER ALLOY

2. FINISH:  
 DIMMING CONTACTS (2 OR 4): NICKEL UNDERPLATE ENTIRE CONTACT 0.127  $\mu$ m MIN THICK. GOLD PLATE CONTACT PAD AREA (MATING FACE SIDE ONLY) 0.76  $\mu$ m MIN THICK. MATTE TIN PLATE TAB ON BOTH SIDES 0.30  $\mu$ m MIN THICK. LINE VOLTAGE CONTACTS (3): TIN PLATE.

3. LINE VOLTAGE CONDUCTORS (3):  
 14 AWG, 600V, 150°C RATED, COPPER 41/30 STRANDED PER UL STYLE AWM 3321.

4. MATING INTERFACE PER ANSI C136.41-2013.

5. OPTIONAL DIMMING CONTACTS (2) SUPPLIED.

6. DIMMING CONDUCTORS (2 OR 4):  
 18 AWG, 600V, 150°C RATED, 16/30 STRANDED, PER UL STYLE AWM 3321.

7. LINE VOLTAGE CONDUCTORS (3):  
 14 AWG, 600V, 105°C RATED, COPPER 41/30 STRANDED. PER UL STYLE AWM 1015.

LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD		
	A20	REVISED PER ECR-20-016246	07DEC2020	MM	JL		
	A21	REVISED PER ECR-21-110497	17AUG2021	JL	MM		
	B	REVISED PER ECR-21-118984	11NOV2021	SD	MM		
	B1	REVISED PER ECR-22-127557	24JAN2022	SD	MM		

8. DIMMING CONDUCTORS (2 OR 4):  
 18 AWG, 600V, 105°C RATED, COPPER 16/30 STRANDED. PER UL STYLE AWM 1015.

9. PRELIMINARY.

10. FOR PART NUMBER 5-2213362-4 ONLY,  
 STRIP AND REMOVE INSULATION AS SHOWN.  
 LEAD WIRES TO BE SOLDER DIPPED.

11. MUST BE USED WITH EITHER GASKET P/N 2213469-1  
 OR P/N 2324246-1 (SOLD SEPARATELY).

SEE SHEET 2 FOR  
 WIRING COLOR CODE

STRIP LENGTH	OVERALL LENGTH	A	B	WIRE STYLE	QUANTITY OF DIMMING CONTACTS	PART NO.
12.0	203.0	153.0	153.0	7 AND 8	4 5	9-2213362-4
12.7	1036.3	1000	986.5	7 AND 8	4 5	8-2213362-4 9
12.7	266.3	230.0	216.5	7 AND 8	4 5	7-2213362-4
12.7	236.3	200.0	-	7	-	6-2213362-4 9
12.7	341.1	304.8	-	3	-	6-2213362-2
12.7	341.1	304.8	-	7	-	6-2213362-1
15.88	264.9	228.6	-	3	-	5-2213362-9
BLACK WIRE: 15.88 WHITE WIRE: 15.88 RED WIRE: 6.35	798.3	762.0	-	3	-	5-2213362-8
9.0	341.1	304.8	291.3	7 AND 8	4 5	5-2213362-4 10 9
9.0	211.3	175.0	175.0	7 AND 8	4 5	4-2213362-6
9.0	341.1	304.8	291.3	7 AND 8	4	4-2213362-5
12.7	950.7	914.4	914.4	7 AND 8	4 5	4-2213362-4 9
8.0	73.0	35.0	35.0	7 AND 8	4 5	3-2213362-4 9
12.7	1865.1	1828.8	1815.3	3 AND 6	2	3-2213362-1 9
12.7	736.3	700.0	686.5	7 AND 8	4 5	2-2213362-4
12.7	696.3	660.0	646.5	3 AND 6	4 5	2-2213362-2 9
12.7	696.3	660.0	646.5	3 AND 6	2	2-2213362-1
12.7	536.3	500.0	486.5	7 AND 8	4 5	1-2213362-4
12.7	536.3	500.0	486.5	7 AND 8	2	1-2213362-3 9
12.7	1823.3	1346.0	1332.5	3 AND 6	4 5	1-2213362-2
12.7	536.3	500.0	486.5	3 AND 6	2	1-2213362-1 9
12.7	341.1	304.8	291.3	7 AND 8	4 5	2213362-4
12.7	341.1	304.8	291.3	7 AND 8	2	2213362-3
12.7	341.1	304.8	291.3	3 AND 6	4 5	2213362-2
12.7	341.1	304.8	291.3	3 AND 6	2	2213362-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	J. SHAFFER	26 JUN 2013
CHK	E. HOWARD	26 JUN 2013
APVD	E. HOWARD	26 JUN 2013

TE Connectivity

RECEPTACLE ASSEMBLY,  
 DIMMABLE PHOTOCONTROL

108-32059  
 APPLICATION SPEC

114-32115  
 WEIGHT


A2 00779 C-2213362

CUSTOMER DRAWING SCALE 1:1 SHEET 1 OF 2 REV B1


1471-9 (3/11)

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20  
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD		
-	-	SEE SHEET 1	-	-	-		



**5-2213362-4 ONLY**



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. SHAFFER 26 JUN 2013	TE Connectivity															
DIMENSIONS: mm		CHK E. HOWARD 26 JUN 2013																
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD E. HOWARD 26 JUN 2013	NAME RECEPTACLE ASSEMBLY, DIMMABLE PHOTOCONTROL															
<table border="0"> <tr><td>0 PLC</td><td>±</td></tr> <tr><td>1 PLC</td><td>±</td></tr> <tr><td>2 PLC</td><td>±0.13</td></tr> <tr><td>3 PLC</td><td>±</td></tr> <tr><td>4 PLC</td><td>±</td></tr> <tr><td>ANGLES</td><td>±</td></tr> <tr><td>FINISH</td><td>±</td></tr> </table>		0 PLC	±	1 PLC	±	2 PLC	±0.13	3 PLC	±	4 PLC	±	ANGLES	±	FINISH	±	PRODUCT SPEC 108-32059	SIZE A200779	
0 PLC	±																	
1 PLC	±																	
2 PLC	±0.13																	
3 PLC	±																	
4 PLC	±																	
ANGLES	±																	
FINISH	±																	
MATERIAL		APPLICATION SPEC 114-32115	DRAWING NO C-2213362															
		WEIGHT -	RESTRICTED TO -															
		CUSTOMER DRAWING	SCALE 1:1 SHEET 2 OF 2 REV B1															